

Twist-Lock® Devices

15A, 277V AC, 2 Pole, 3 Wire Grounding

Receptacle

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Ordering Information

Description	Device Color	UPC	Catalog Number
Duplex, flush, brown	Brown	783585002347	HBL4750

Listings

Listed to UL 498
 Fed. Spec. W-C-596
 Certified to CSA C22.2 No.42

Specifications

Face	RTP
Base	RTP
Contacts	Brass
Clamp	Brass
Ground Contact	Brass
Terminal Screws	Brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
 Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG - #10 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498


Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17
 Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

HUBBELL



15A 277V AC
 NEMA L7-15R
 UL/CSA
 2 HP



Online Resources

Customer Use Drawing
 eCatalog
 Installation Instructions

Accessories

Plug
 Wallplate or Weatherproof Cover

HBL4770C
 1.40" Opening

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

