



71 82 950

Concrete Mesh Cutter



- cutting capacity up to 48 HRC hardness
- robust cutting edges are additionally induction hardened, cutting-edge hardness approx. 62 HRC
- forged-in stopper with comfortable shock- absorber
- good access due to very flat construction of head and joint area
- ergonomically angled handles to minimise effort
- sturdy non-slip two-colour dual component handle sleeves
- precise adjustment (12 positions) by eccentric bolt
- high cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- bolted cutter head, replaceable
- blade: chrome vanadium heavy-duty steel, forged, oil-hardened
- joint: special tool steel, forged
- handles: steel tube, powder-coated

Article No.	71 82 950
EAN	4003773066798
Head	grey atramentized
Handles	with multi-component grips
HRC 19 Ø mm	11
HRC 48 Ø mm	6
HRC 40 Ø mm	9
Cutting edge length mm mm	44
Head thickness mm	40
Length mm	950
Net weight g	4110



The special shape of the mesh cutter head, 71 82 950, enable it to cut structural steel that is lying down flat.

technical change and errors excepted



Spare Parts

Article No.	EAN	
71 89 950	4003773066842	Spare cutter head for 71 82 950 complete with screws