



EAN:	4013288100733	Size:	220x37x37 mm
Part number:	05028054001	Weight:	87 g
Article number:	367 TORX® HF	Country of origin:	CZ

Customs tariff number: 82054000

- Screwdriver for recessed TORX® screws
- Holding function for TORX® screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away

High quality Kraftform Plus screwdriver. Multi-component Kraftform handle for fast and low-fatigue working. Kraftform Plus: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Holding function: the wedging forces resulting from the contact pressure between the drive tip and the screw profile securely hold the screw on the tool. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace. Handle markings for simplified finding and sorting of the tool.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus__series_300_367_torx_hf.html

Wera - 367 TORX® HF
 05028054001 - 4013288100733

TORX® HF profile



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.

Kraftform



In tight assembly or disassembly situations, for example in engine compartments, it is not possible to securely hold the screw with the hand on the screwdriver, and the screw subsequently often gets lost. Lengthy searches or the loss of the screw (with the associated danger that could bring about) are the consequence. The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that the screw is securely held on the tool!

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

Large contact area




The large contact area – with particularly high friction to the soft zones – results in high torque transfer without any bruising from the edges.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus__series_300_367_torx_hf.html

Wera - 367 TORX® HF
05028054001 - 4013288100733

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

						
			mm	mm	mm	inch
05028048001	TX 8		60	81	3.5	2 3/8
05028049001	TX 9		60	81	4.0	2 3/8
05028050001	TX 10		80	81	4.0	3 1/8
05028051001	TX 15		80	98	4.0	3 1/8
05028052001	TX 20		100	98	4.5	4
05028070001	TX 20		300	98	4.5	12
05028053001	TX 25		100	105	5.0	4
05028071001	TX 25		300	105	6.0	12
05028054001	TX 27	115		105	5.5	4 9/16
05028072001	TX 27		300	105	6.0	12
05028055001	TX 30		115	105	6.0	4 9/16
05028073001	TX 30		300	105	6.0	12
05028056001	TX 40		130	112	7.0	5 3/16

Web link
https://products.wera.de/en/screwdrivers_kraftform_plus__series_300_367_torx_hf.html

Wera - 367 TORX® HF

05028054001 - 4013288100733

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de