



**MCR  
SAFETY**

**N9680**

**Ninja**

**Dipped**

**Specification Sheet**

**PRODUCT DESCRIPTION:**

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Flex features, 15 gauge red nylon shell and gray latex coated palm and fingertips.

**FEATURES:**

- 15 Gauge Red Nylon Shell
- Gray Latex Coated Palm and Fingertips
- CE Score 3131
- Great Fit and Grip

**APPLICATIONS:**

Automotive Assembly, Farming, Landscaping, Material Handling, Agriculture, Carpentry, Construction, Furniture industry, Janitorial, Manufacturing, Mechanics, Sanitation, Warehousing



**TECHNICAL DATA FOR: N9680**

<b>Series</b>	Ninja	<b>EN 388 : CE Score - Abrasion</b>	3
<b>Material Group</b>	Strings	<b>EN 388 : CE Score - Cut</b>	1
<b>Product Type</b>	Dipped	<b>EN 388 : CE Score - Tear</b>	3
<b>Glove Size</b>	Large	<b>EN 388 : CE Score - Puncture</b>	1
<b>Gauge</b>	15 Gauge	<b>ANSI Abrasion</b>	ANSI Abrasion 4
<b>Material</b>	Nylon		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

# N9680

## Ninja

### Dipped

#### Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9680L	Large	9.84	4.75	3	25.812 lb.	2.151
N9680M	Medium	9.25	4.39	2.85	24.096 lb.	2.008
N9680S	Small	8.66	3.85	2.50	22.020 lb.	1.835
N9680XL	X - Large	10.43	5.50	3	26.856 lb.	2.238
N9680XXL	XX - Large	11.89	6.25	3.87	27.912 lb.	2.326

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved