

## Food Grade Scrapers

Hygiene | Sanitation | Safety



Remco Products offers a variety of FDA-compliant scrapers for all your scraping, bench top and food prep needs. As part of a comprehensive line of hygienic material handling tools, Remco and Vikan scrapers are designed to minimize the risk of cross-contamination in wet or dry food processing. One-piece construction helps eliminate areas for bacteria to hide in and multiply. The scrapers are also chemical resistant and autoclavable. Available in a vast array of colors, these scrapers support color-coding programs and hygienic sanitary and safety procedures throughout food processing facilities.

# Floor Scrapers



Remco Products offers an assortment of food-safe scrapers designed with hygiene and durability in mind. The food hoe, floor scrapers, and paddle scrapers are designed to be paired exclusively with Vikan or Remco handles only. For more on these handle options, see our Handle Selection Guide, our Full-Line Catalog, or visit [remcoproducts.com](http://remcoproducts.com).

## Food Hoe - 2900x



**REMCO**

Colors Available:	② ③ ④ ⑤ ⑥	
Length:	Width:	Height:
2.0"	11.25"	8.0"
Weight:	1.13 lbs.	
Deflection / Softening Temps:	410°F / 419°F	
Material:	Nylon	




Green Blue Red White Yellow

## Stainless Steel Floor Scraper - 2910x



**Vikan**

Colors Available:	② ③ ④ ⑤ ⑥ ⑨	
Length:	Width:	Height:
10.25"	1.25"	6.9"
Weight:	0.56 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Stainless Steel	



Green Blue Red White Yellow Black

## Nylon Floor Scraper - 2911x




**REMCO**

Colors Available:	② ③ ④ ⑤ ⑥ ⑨	
Length:	Width:	Height:
10.25"	1.0"	6.9"
Weight:	0.65 lbs.	
Deflection / Softening Temps:	410°F / 419°F	
Material:	Nylon	



Green Blue Red White Yellow Black

 Denotes product is made of FDA compliant materials.

 Denotes product is autoclavable to 250°F.

 Denotes product is dishwasher safe to 176°F.

# Hand and Bench Scrapers




**REMCO**

## 3" Scraper - 6961x | 4" Scraper - 6962x



Colors Available:	1 2 3 4 5 6 7 8 9		
Length:	Width:	Height:	
0.1"   0.2"	3.0"   4.3"	8.1"   9.8"	
Weight:	0.09 lbs.   0.18 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene		



Pink Green Blue Red White Yellow Orange Purple Black



**REMCO**

## 4" High Temperature Scraper - 6963



Colors Available:	Blue		
Length:	Width:	Height:	
0.1"	4.5"	10.0"	
Weight:	0.3 lbs.		
Deflection / Softening Temps:	424°F / 392°F		
Material:	Nylon/Fiberglass		



Blue



**REMCO**

## 1.5" SS Scraper - 6971x | 3" SS Scraper - 6972x



Colors Available:	1 2 3 4 5 6 7 8 9		
Length:	Width:	Height:	
0.1"	1.5"   3.0"	8.9"	
Weight:	0.21 lbs.   0.25 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene/Stainless Steel		



Pink Green Blue Red White Yellow Orange Purple Black



**REMCO**

## 5" Mini Bench Scraper - 6959x



Colors Available:	1 2 3 4 5 6 7 8 9		
Length:	Width:	Height:	
0.2"	5.25"	7.3"	
Weight:	0.09 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene		



Pink Green Blue Red White Yellow Orange Purple Black



**REMCO**

## 8" Bench Scraper - 6960x



Colors Available:	1 2 3 4 5 6 7 8		
Length:	Width:	Height:	
0.2"	8.3"	5.2"	
Weight:	0.29 lbs.		
Deflection / Softening Temps:	183°F / 266°F		
Material:	Polypropylene		



Pink Green Blue Red White Yellow Orange Purple

Denotes product is made of FDA compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

# Paddle Scrapers



**REMCO**

## 40" Mixing Paddle - 6774x (w/ Holes) | 6775x (w/o Holes)

Colors Available:	② ③ ④ ⑤ ⑥	
Length:	Width:	Height:
39.75"	6.0"	1.4"
Weight:	2.11 lbs.   2.19 lbs.	
Deflection / Softening Temps:	183°F / 266°F	
Material:	Polypropylene	



**REMCO**

## 52" Mixing Paddle - 6776x (w/ Holes) | 6777x (w/o Holes)

Colors Available:	② ③ ④ ⑤ ⑥	
Length:	Width:	Height:
51.8"	5.9"	1.4"
Weight:	2.64 lbs.   2.66 lbs.	
Deflection / Softening Temps:	183°F / 266°F	
Material:	Polypropylene	



**Vikan**


## Paddle Scraper - 7011x (Rigid) | 7013x (Flexible)

Colors Available:	② ③ ④ ⑤ ⑥	
Length:	Width:	Height:
8.75"	4.3"	1.0"
Weight:	0.32 lbs.   0.26 lbs.	
Maximum Temperature:	338°F   176°F	
Material:	Nylon   Polyethylene	



Remco also offers a line of Metal Detectable Scrapers. For more information, call **317.876.9856**, email [cs@remcoproducts.com](mailto:cs@remcoproducts.com) or visit [remcoproducts.com](http://remcoproducts.com).

 Denotes product is made of FDA compliant materials.

 Denotes product is autoclavable to 250°F.

 Denotes product is dishwasher safe to 176°F.

### Remco Products Corporation

4735 West 106th Street | P.O. Box 698  
Zionsville, Indiana 46077

PHONE: 317.876.9856 | FAX: 800.585.8619

[www.remcoproducts.com](http://www.remcoproducts.com)

© 2014 Remco Products 12/16 RMC-B107 | Vikan® is a registered trademark of Vikan A/S. | Remco is the exclusive Vikan Partner in the United States.

**REMCO**

