

REMCO

Material Handling Tools

Hygienic | Sanitary | Safe

Material handling solutions for hygiene sensitive environments



Remco material handling tools are carefully designed and produced from materials that comply with regulatory standards. Any tool that contacts food should be backed by the appropriate documentation to support a written food safety plan, which we can provide to all our customers. Our superior tools are ergonomically built, eliminating excessive stress and strain on the user. This improves the productivity of your workforce and ultimately your overall operation.



Remco shovels and scoops are made from durable and lightweight polypropylene and won't damage equipment, unlike metal tools. Remco tubs and undercarriages are ideally designed for many bulk material handling jobs that require containers made of FDA-compliant materials. Constructed with high-density polyethylene, they can be used for transporting, freezing, and storing.

REMCO One-Piece Shovel
w/ 10" Blade
6981x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
37.5"	10.2"	5.9"
Weight:	2.60 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		


REMCO One-Piece Shovel
w/ 14" Blade
6982x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
42.5"	13.75"	6.6"
Weight:	3.56 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO One-Piece Dual Grip
Shovel w/ 14" Blade
6984x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
47.5"	13.6"	6.25"
Weight:	4.84 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 32 oz. Hand Scoop
6400x



Colors Available: 1 2 3 4 5 6 7 8

Length:	Width:	Height:
11.5"	4.3"	3.0"
Weight:	0.39 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 82 oz. Hand Scoop
6500x



Colors Available: 1 2 3 4 5 6 7 8

Length:	Width:	Height:
15.1"	5.9"	3.3"
Weight:	0.65 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 128 oz. Mega Scoop
6550x



Colors Available: 2 3 4 5 6 7

Length:	Width:	Height:
11.0"	8.7"	6.7"
Weight:	1.35 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		



Scraping tools from Remco offer solutions for a variety of bench top, food prep, and floor applications. These tools are ideal when you need a hygienic option for effectively moving materials, and are rigid enough to perform without bending or breaking. See our full line catalog or visit remcoproducts.com for a complete list of scrapers and material handling tools offered by Remco Products.

REMCO 5" Mini Bench Scraper
6959x

Now in Additional Colors!



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
0.31"	5.25"	3.4"
Weight: 0.09 lbs.		
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 8" Bench Scraper
6960x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
0.2"	8.3"	5.2"
Weight: 0.29 lbs.		
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 3" Scraper
6961x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
0.1"	3.0"	8.1"
Weight: 0.09 lbs.		
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 4" Scraper
6962x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
0.2"	4.3"	9.8"
Weight: 0.18 lbs.		
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 1.5" Stainless Steel Scraper
6971x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
1.0"	1.5"	8.9"
Weight: 0.21 lbs.		
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene / Stainless Steel		

REMCO 3" Stainless Steel Scraper
6972x



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
1.0"	3.0"	8.9"
Weight: 0.25 lbs.		
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene / Stainless Steel		

Denotes product is made of FDA-compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

REMCO Nylon Floor Scraper
2911x



Colors Available: 2 3 4 5 6 9

Length:	Width:	Height:
10.25"	1.0"	6.9"
Weight:	0.65 lbs.	
Deflection / Softening Temps: 410°F / 419°F		
Material: Nylon		

REMCO 40" Mixing Paddle
6775x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
39.75"	6.0"	1.4"
Weight:	2.19 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO 52" Mixing Paddle
w/ Holes
6776x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
51.8"	5.9"	1.4"
Weight:	2.64 lbs.	
Deflection / Softening Temps: 183°F / 266°F		
Material: Polypropylene		

REMCO Angled Dump Tub
6901x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
54.6"	32.0"	21.7"
Weight:	28.00 lbs.	
Deflection/Softening Temps: 173°F to 258°F		
Material: Polyethylene		

REMCO Angled Dump Tub Lid
6902x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
56.0"	32.0"	4.3"
Weight:	15.00 lbs.	
Deflection/Softening Temps: 173°F to 258°F		
Material: Polyethylene		

REMCO Regular Undercarriage
6903



Colors Available: Steel

Length:	Width:	Height:
41.1"	27.3"	19.1"
Weight:	69.50 lbs.	
Material: Galvanized Steel		

REMCO Transport Storage Tub
6911x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
46.8"	26.5"	16.9"
Weight:	20.50 lbs.	
Deflection/Softening Temps: 173°F to 258°F		
Material: Polyethylene		

REMCO Transport Storage
Tub Lid
6912x



Colors Available: 2 3 4 5 6

Length:	Width:	Height:
46.9"	26.9"	1.7"
Weight:	10.50 lbs.	
Deflection/Softening Temps: 173°F to 258°F		
Material: Polyethylene		

REMCO Galvanized Steel
Undercarriage
6913



Colors Available: Steel

Length:	Width:	Height:
42.5"	21.6"	9.4"
Weight:	57.50 lbs.	
Material: Galvanized Steel		

Denotes product is made of FDA-compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

Visit our website at www.remcoproducts.com for a full selection of products.

Remco Products Corporation

4735 West 106th Street
Zionsville, Indiana 46077

Phone: 317.876.9856 | Fax: 800.585.8619

Email: sales@remcoproducts.com

www.remcoproducts.com

© 2017 Remco Products 4/17 RMC-A110 Vikan® is a registered trademark of Vikan A/S. Remco is the exclusive Vikan Partner in the United States.

