




Technical Specs

	6PY48	6PY55
SHIPPING WEIGHT	45.3 LBS	45.2 LBS
MAXIMUM LIQUID TEMPERATURE	212°F (100°C)	212°F (100°C)
INTAKE & DISCHARGE PORTS	1" PORT, NPT	1" PORT, NPT
FLOW	0 - 49 GPM MAX	0 - 35 GPM MAX
MAX AIR SUPPLY PRESSURE	100 PSI (1.4 - 7 KGF/CM ²)	100 PSI (1.4 - 7 KGF/CM ²)
BODY MATERIAL	STAINLESS STEEL	STAINLESS STEEL
LIFT - DRY, WET	18 FT, 28 FT	15 FT, 28 FT
AIR VALVE		
LUBRICATION	NO LUBRICATION REQUIRED	NO LUBRICATION REQUIRED
MANUAL OVERRIDE	YES	YES
LIQUID SIDE		
EASY REPAIR	YES	YES
BALL CHECK VALVE	EPDM	PTFE
O-RINGS	EPDM	PTFE
DIAPHRAGMS	SANTOPRENE®	SANTOPRENE®


DAYTON AIR-OPERATED DOUBLE DIAPHRAGM PUMP

6PY48, 6PY55


Dimensional Drawing



Performance Curve



6PY48



6PY55

Find it at Grainger.

Call or visit your local branch or go to grainger.com/dayton for complete product line information.

Dayton®