



## SINGLE CYLINDER DOLLY™ HD

Just as durable and half the size. The Single Cylinder Dolly™ HD is designed for demanding industrial facilities or tough outdoor applications in which transport of a single cylinder is required. Accommodates one cylinder, up to 12" in diameter, including class 300 SCF industrial gas cylinders and No. 5 acetylene cylinders.

Rugged, solid wheels standard on Part # 7301-BK-A to maximize maneuverability over rough terrain.

## DUAL CYLINDER DOLLY™

**EASIER CYLINDER LOADING, BETTER MANEUVERABILITY, AND LARGE TRAY FOR TOOLS.**

The Dual Cylinder Dolly™ is designed to be a more functional, maneuverable, and better balanced transporter for gas cylinders than conventional dollies or forklifts. Ideal for industrial or construction operations, the Dual Cylinder Dolly™ can accommodate a variation of two cylinders including class 300 SCF industrial gas cylinders and No. 5 acetylene cylinders. Specifically designed for joint movement of multi-sized cylinders with featured 10" and 12" compartments to guarantee your cylinder's perfect fit!

The dolly's lightweight yet durable polyethylene construction and effective counter balancing makes it easy to handle with minimum physical effort. Tough 16.5" diameter pneumatic wheels offer the best maneuverability over any terrain.

Unlike metal cylinder carts, the Dual Cylinder Dolly™ is spark-resistant and the rugged polyethylene construction will not rust or corrode under harsh weather conditions.



36" built-in tray holds tools, valves and torches.

### CYLINDER DOLLY™

Part #	Description	Dimensions LxWxH in. (cm)	Weight lb. (kg)	Load Cap. lb. (kg)
7301-BK	Single HD	23.75 x 23 x 46 (60 x 58 x 117)	26.8 (12.2)	250 (113.4)
7301-BK-A	Single HD ATD	23.75 x 23 x 46 (60 x 58 x 117)	39 (17.7)	250 (113.4)
7302-BK	Dual	37 x 23.5 x 45 (94 x 60 x 114)	56.9 (25.8)	500 (227)

Regulations: OSHA 29 CFR 1910.253

## UNIVERSAL CYLINDER BRACKET™

Ideal for low-cost wall or truck mounted storage. Design your own configuration to hold one, two, three, or x amount of cylinders with extendable modular flexibility. Units link together to customize the amount of cylinders needed. Attaches to any wall or truck bed securely and easily. Accommodates cylinders from 3" to 10" in diameter and saves space on any wall. Straps included.



**ENHANCED DESIGN**



### CYLINDER BRACKET™

Part #	Description	Dimensions LxWxH in. (cm)	Weight lb. (kg)
7216-YE	Universal Cylinder Bracket	15.3 x 6.3 x 3.3 (38.7 x 15.9 x 8.3)	1 (.5)

Regulations: OSHA 29 CFR.1910