

# A11 Series Low Temperature Cutout Controls

## Product Bulletin

A11A, A11B, A11D, A11E

**Code No. LIT-125010**  
**Issued December 7, 2012**  
*Supersedes August 1, 1990*

Refer to the [QuickLIT Web site](#) for the most up-to-date version of this document.

A11 Series low temperature cutout controls are available with Single-Pull, Single-Throw (SPST) or Single-Pull, Double-Throw (SPDT) contact action. Typical applications include the sensing of low temperature conditions to avoid over cooling or icing of hydronic coils, cooling coils, and liquid-handing pipes. The controls are compact and sturdy, and have an adjustable temperature setpoint range with a fixed differential. The range adjustment screw is accessible at the bottom of the control, and at the top of the control when the cover is removed.



**Figure 1: A11 Series Low Temperature Cutout Control**

**Table 1: Features and Benefits**

<b>Features</b>	<b>Benefits</b>
<b>Precision Repeat Accuracy</b>	Remains unaffected by ambient temperature at the control diaphragm cup and 4 ft (1.2 m) capillary (20 ft [6.1 m] sensing bulb must be in the controlled area).
<b>Trip-Free Manual Reset</b>	Allows the lever to reset. You must press and release the lever before operation resumes.
<b>Recision Snap-Acting Contacts in a Dust Protected Enclosure</b>	Enables the A11 to operate to the fullest potential.
<b>Direct Reading Scale</b>	Provides easy to adjust setpoint. Adjustments can be made from the top or bottom of the control.

## Overview

The A11 controls are compact and sturdy and feature an adjustable range with a fixed differential. The range adjustment screw is accessible at the bottom of the control or at the top, when the cover is removed. A factory-set low temperature stop is available when specified.

Figure 2 shows the A11 dimensions. Figure 2 describes the A11 electrical ratings.




Figure 2: A11 Series Low Temperature Cutout Controls Dimensions, in. (mm)

Table 2: Electrical Rating

Motor Rating	120 V	208 V	240 V
Motor Description			
AC Full Load Amperes	16.0	9.2	8.0
AC Locked Rotor Amperes	96.0	55.2	48.0
Non-Inductive Amperes	16.0	9.2	8.0
Pilot Duty - 125 VA, 24 to 277 VAC			

## Ordering Information

Table 3 describes the A11 Series Low Temperature Cutout Control models.

Table 3: A11 Models

Model	Description
A11A	Single-Pull, Single-Throw (SPST), Open Low, Manual Reset
A11B	SPST, Open Low, Automatic Recycle
A11D	Single-Pull, Double Throw (SPDT), Manual Reset
A11E	SPDT, Automatic Recycle

When ordering an A11 Series Low Temperature Cutout Control:

1. Specify the product number.
2. Specify the low temperature cutout stop setting, if necessary.

## Repairs and Replacements

If the A11 Series Low Temperature Cutout Control fails to operate within its specifications, replace the unit. Contact your nearest Johnson Controls® representative.

## Technical Specifications

### A11 Low Temperature Cutout Controls

<b>Product Codes</b>	A11A: SPST, Open Low, Manual Reset A11B: SPST, Open Low, Automatic Recycle A11D: SPDT, Manual Reset A11E: SPDT, Automatic Recycle	
<b>Range Cutout</b>	35 to 45°F (2 to 7°C)	
<b>Differential</b>	<b>A11A and A11D:</b> Temperature must be 12°F (6.7°C) above cutout point before control can be reset. <b>A11B and A11E:</b> 12°F (6.7°C)	
<b>Ambient Temperature</b>	<b>Minimum:</b> 0°F (-18°C) <b>Maximum:</b> 140°F (60°C)	
<b>Maximum Temperature at Bulb</b>	250°F (121°C)	
<b>Sensing Element</b>	1/8 in. x 20 ft (3.2 mm x 6.1 m) or 1/8 in. x 40 ft (3.2 mm x 12.2 m)	
<b>Capillary Length</b>	4 ft (1.2 m)	
<b>Switch</b>	Snap-acting contacts in dust-protected enclosure	
<b>Material</b>	<b>Case:</b> 0.6 (1.6 mm) Cold Rolled Steel <b>Cover:</b> 0.3 in. (0.8 mm) Cold Rolled Steel	
<b>Finish</b>	Galvanized Steel	
<b>Conduit Opening</b>	22 mm (0.9 in.) hole for 12.7 mm (1/2 in.) conduit	
<b>Mounting Bracket</b>	Standard on all controls	
<b>Shipping Weight</b>	<b>Individual Pack:</b> 1.8 lb (0.8 kg) <b>Overpack of 20 Units:</b> 38 lb (17 kg)	
<b>Electrical Rating</b>	<b>Pilot Duty:</b> 125 VA, 24 to 277 VAC	
<b>Motor Ratings</b>	<b>AC Full Load Ampere:</b> 120 V = 16.0 A, 208 V = 9.2 A, 240 V = 8.0 A <b>AC Locked Rotor Ampere:</b> 120 V = 96.0 A, 208 V = 55.2 A, 240 V = 48.0 A <b>Non-Inductive Ampere:</b> 120 V = 16.0 A, 208 V = 9.2 A, 240 V = 8.0 A	
<b>Compliance</b>	<b>United States</b>	UL Listed, File SA516, SDFY
		FCC Compliant to CFR 47, Part 15 Subpart B, Class A
	<b>Canada</b>	UL Listed, CSA Class No. 1222 01, File LR948
		Industry Canada, ICES-003

The performance specifications are nominal and conform to acceptable industry standards. For application at conditions beyond these specifications, consult the local Johnson Controls office. Johnson Controls, Inc. shall not be liable for damages resulting from misapplication or misuse of its products.



**Building Efficiency**  
507 E. Michigan Street, Milwaukee, WI 53202

Metasys® and Johnson Controls® are registered trademarks of Johnson Controls, Inc. All other marks herein are the marks of their respective owners. © 2012 Johnson Controls, Inc.