

Hazardous Location Handlamps

Illuminate your hazardous location work areas easily and safely with this LED explosion proof handlamp. Made with tough, durable, certified and proven LED hazardous location lights, this handlamp will meet the OSHA requirements for lighting a construction area while keeping your workers safe. The rugged Tuffite handle and aluminum guard make this a mainstay of the hazardous location line.

Customizable options are available by adding an explosion proof plug or a different length or type of cord.

Standard models include 16/3 SOOW cord and non-explosion proof plug.



SPECIFICATIONS	
VOLTAGE	120V light
WATTAGE	9W replaceable LED bulb (60W equivalent)
LUMENS	800 lumens per bulb
CONSTRUCTION	5-15P non-explosion proof plug, 50' of 16/3 SOOW cord
LENGTH & DIAMETER	18.5" x 5"
WEIGHT	4lbs
CLASS/DIVISION	cULus certified Class 1, Division 1, Groups C & D (CSA and UL Standards)

PART OPTIONS	
XP162LED	100W 120V hand lamp only.
XP162LED-25P	with 25' cord and plug.
XP162LED-50P	with 50' cord and plug.
XP162LED-100P	with 100' cord and plug.
REPLACEMENT LED: P/N XP162-P1	



For more information about our other lines of portable electrical equipment for the toughest workplaces: www.lindequipment.net | info@lindequipment.net | T: 877.475.LIND

