




## DAYTON AIR-OPERATED DOUBLE DIAPHRAGM PUMP

22A594



SHIPPING WEIGHT	28 LBS
MAXIMUM LIQUID TEMPERATURE	180°F (82°C)
INTAKE & DISCHARGE PORTS	1-1/2" x 1-1/4" PORT NPT
FLOW	0 - 50 GPM MAX
MAX AIR SUPPLY PRESSURE	100 PSI (1.4 - 7 KGF/CM <sup>2</sup> )
BODY MATERIAL	ALUMINUM
LIFT - DRY, WET	18 FT, 28 FT
<b>AIR VALVE</b>	
LUBRICATION	NO LUBRICATION REQUIRED
MANUAL OVERRIDE	YES
<b>LIQUID SIDE</b>	
EASY REPAIR	YES
BALL CHECK VALVE	BUNA N
O-RINGS	BUNA N
DIAPHRAGMS	BUNA N



Find it at Grainger.

Call or visit your local branch or go to [grainger.com/Dayton](http://grainger.com/Dayton) for complete product line information.