

**NORTON**

SAINT-GOBAIN

## NORTON MULTI-AIR NORGRIP PAPER DISCS AND FILE STRIPS

EXPANDED  
OFFERING

**MULTI** **AIR.**

**AEROSPACE MANUFACTURING**

**AIRCRAFT REFINISHING**

**COMPOSITE**

**PRIME AUTO**

**SOLID SURFACE**

**WIND ENERGY**

**WOOD**




[www.nortonabrasives.com](http://www.nortonabrasives.com)

LESS DUST MEANS  
**MORE PRODUCTIVITY**

# NEW TECHNOLOGY IN SANDING


## The Multi-Air Process

Eliminating dust and increasing the surface cutting area are how the Multi-Air process is able to improve productivity by 35% versus traditional vacuum sanding and by 60% versus non-vacuum sanding. It's simple, if you keep the abrasive grain exposed by continually removing the dirt that can clog paper and leave wild scratches, you will cut faster and the sandpaper will last longer. Bottom line, the job gets done faster and costs less with Norton Multi-Air discs and file strips.



## Sand More in Less Time!

The Multi-Air process eliminates dust. This keeps the surface of the disc and file strip clean allowing the abrasive grains to continue cutting substantially longer and faster than conventional systems.



- 35% productivity gain over traditional vacuum sanding
- 60% productivity gain over traditional non-vacuum sanding
- May be used with a self-generating D/A vacuum tool for workplaces without a central vacuum system
- Virtually no clogging
- Revolutionary, highly engineered back-up pad and blocks for maximum dust extraction
- Elimination of dust gives the technician full visual control of the work surface and longer product life
- Reduce contaminants in the workplace
- Cleaner working environment
- Sand more in less time

### FEATURES

- Drylce A975; patented Norton SG ceramic abrasive
- Norton BlueMag H835; coarse grit, non-stearated advanced zirconia grain; stiff durable E-wt backing
- Original performance A275; premium, heat-treated aluminum oxide grain
- A270; non-stearated, non-contaminating premium, heat-treated aluminum oxide grain
- A475; sharp, silicon carbide abrasive the hardest man-made abrasive next to diamond
- Unique SoftTouch discs in fine grits

### BENEFITS

- Fastest cut rate; longest life; designed for the most demanding sanding jobs
- Grain micro-fractures, remaining sharp and fast-cutting; ideal for more aggressive sanding applications
- Superior life, fast-cut, consistent finish
- Fast cutting action with consistent finishes (often required for prime auto and aerospace paint jobs)
- Ideal for use on tooling gel coats, conventional gel coats, hard composite substrates, and abrasion-resistant coatings
- Sand over contours without cutting through

**NORTON**

SAINT-GOBAIN




# THE MULTI-AIR ADVANTAGE

## Multi-Air Discs


The Norton Multi-Air process combines the revolutionary maximum dust extraction Multi-Air back-up pad with premium abrasive Multi-Air discs to optimize performance, increase productivity, and eliminate dust.

INNOVATION IS IN THE AIR



## Multi-Air File Strips

The family of Norton Multi-Air products has expanded to include Multi-Air file strips and blocks. This simple but effective system works using Multi-Air hand blocks, and a self-generating vacuum file machine that can be used with a portable or central vacuum system. This innovative sanding process will virtually eliminate dust in your workplace which means more productivity, better quality workpieces, and a cleaner work environment.



LESS DUST MEANS  
MORE PRODUCTIVITY



# MULTI-AIR DISC AVAILABILITY



## No-Fil Multi-Air A975 NorGrip Discs

DryIce, patented Norton SG ceramic aluminum oxide abrasive. Designed for the most demanding DA sanding applications on painted parts including composites and marine gel.



## No-Fil Multi-Air A275 NorGrip Discs

A275 "Original Performance" aluminum oxide NorGrip discs offer extra long life and fast cut rate for any sanding job.



## Multi-Air H835 NorGrip Discs

Norton BlueMag H835 hook and loop NorGrip discs last long and cut quickly using coarse grit, non-stearted advanced zirconia grain, which micro-fractures to remain sharp-cutting. Stiff durable E-wt backing for more aggressive sanding applications

BEST		
SIZE	UPC	GRIT
5" x 11/16"	63642563535	P80
100 discs/pack	63642563536	P120
4 packs/case	63642563537	P150
	63642563538	P180
	63642563539	P220
	63642563540	P240
	63642563541*	P280
	63642563542	P320
	63642563543	P400
6" x 11/16"	63642506243	P80
50 discs/pack	66254412469*	P100
4 packs/case	63642506244	P120
	63642506245	P150
	63642506246	P180
	63642506247	P220
	63642506248	P240
	63642506249	P280
	63642506250	P320
	63642506251	P400
	63642506252	P500
	63642506253	P600
	63642506254	P800
8" x 3/4"	66254460398*	P80
100 discs/pack	66254460399*	P100
4 packs/case	66254460400*	P120
	66254460401*	P150
	66254460403*	P180
	66254460404*	P220
	66254460405*	P240

\* NON-STOCK; CALL FOR NON-STOCK QUOTATION.  
5" AND 6" DISCS: MINIMUM QUANTITY = 2,000 DISCS.  
8" DISCS: MINIMUM QUANTITY = 1,200 DISCS

BETTER		
SIZE	UPC	GRIT
5" x 11/16"	63642563520	P320
	63642563521*	P360
	63642563522	P400
	63642563523	P500
	63642563524*	P600
	63642563525	P800
6" x 11/16"	63642560561	P80
	63642560562*	P120
	63642560563	P150
	63642560564	P180
	63642560565	P220
	63642560566	P240
	63642560567	P280
	63642560568	P320
	63642560569*	P360
	63642560570	P400
	63642560571	P500
	63642560572	P600
	63642560573	P800
8" x 3/4"	66254460406*	P80
	66254460407*	P100
	66254460408*	P120
	66254460410*	P150
	66254460412*	P180
	66254460413*	P220
	66254460414*	P240
	66254460415*	P280
	66254460416*	P320

100 DISCS/PACK – 4 PACKS/CASE

\* NON-STOCK; CALL FOR NON-STOCK QUOTATION.  
5" AND 6" DISCS: MINIMUM QUANTITY = 2,000 DISCS.  
8" DISCS: MINIMUM QUANTITY = 1,200 DISCS

BEST		
SIZE	UPC	GRIT
6" x 11/16"	66261181412	P80


50 DISCS/PACK – 4 PACKS/CASE



MORE PRODUCTIVITY MEANS  
MORE PROFIT



# MULTI-AIR DISC AND BACK-UP PAD AVAILABILITY




## Multi-Air A270 NorGrip Discs

A270 non-stearted (no anti-loading agents), non-contaminating premium, heat-treated aluminum oxide grain makes these discs ideal for prime auto and aerospace paint applications.

BETTER		
SIZE	UPC	GRIT
5" x 11/16"	66261071087*	P320
	66261029749*	P400
	66261029750*	P500
	66254469392*	P600
	66254412761*	P800
	66254476828*	P1000

\* NON-STOCK; CALL FOR NON-STOCK QUOTATION.  
MINIMUM QUANTITY = 2,000 DISCS.



## No-Fil Multi-Air A475 NorGrip Discs

A475 sharp, silicon carbide (the hardest man-made abrasive next to diamond) discs, specifically designed for sanding and finishing hard surfaces, e.g. tooling gel coats, conventional gel coats, hard composite substrates, and abrasion-resistant coatings.

BETTER		
SIZE	UPC	GRIT
5" x 11/16"	66254469673*	P150
	66254469674*	P180
6" x 11/16"	66254469675*	P150
	66254469677*	P180
	66261052264*	P400
	66254433565*	P600
	66261052257*	P800
	66261052256*	P1000

\* NON-STOCK; CALL FOR NON-STOCK QUOTATION.  
MINIMUM QUANTITY = 2,000 DISCS.



## No-Fil Multi-Air SoftTouch A275 NorGrip Discs

These A275 "Original Performance" aluminum oxide SoftTouch NorGrip discs are designed with 4mm of foam laminated between the sandpaper and the loop fabric for contour sanding without cutting through.

BETTER			
SIZE	UPC	GRIT	
6" x 11/16"	63642560577	P800	Blue
	63642560578	P1000	White
	63642560579	P1500	Green

20 DISCS/PACK - 4 PACKS/CASE




## Multi-Air Foam Interface Pads

These new Multi-Air foam interface pads are designed to be used with fine grit NorGrip Multi-Air sanding discs. They allow sanding of contours and improve surface finish. Use with Multi-Air back-up pads.

Do not use with Multi-Air SoftTouch discs.

UPC	DESCRIPTION	STD. PKG.
63642585864	5" pad	16
07660719359	6" pad	12
07660782019	8" pad	10




## Multi-Air NorGrip Back-Up Pads


Our new Multi-Air back-up pads are engineered to work as a system with our Multi-Air discs and enhance the performance of the discs by aligning with the discs' holes to maximize the dust extraction and life of the discs. Pads have longer hooks for maximum hold.

UPC	DESCRIPTION	STD. PKG.
63642582249	5" x 5/16"-24 fixed shank, 1 foam laminate pad, medium density	1
63642582245	6" x 5/16"-24 fixed shank, 1 foam laminate pad, medium density	1
63642506160	6" x 5/16"-24 fixed shank, 1 urethane pad, medium density	1
66254425341	8" for Hutchins	10

## INNOVATION IS IN THE AIR



## MULTI-AIR FILE STRIP AVAILABILITY



### NorGrip Multi-Air Vacuum File Strips

A975 DryIce and H835 BlueMag hook and loop NorGrip file strips are perfect for refinishing jobs that require an extremely durable abrasive grain with a strong reinforced backing that cuts fast plus lasts extra long without generating heat.

BEST		
UPC	GRIT	SPECIFICATION
<b>2-3/4" x 5"</b>		
69957394449	P40	H835
69957394456	P80	A975
69957394457	P120	A975
69957394459	P180	A975
<b>2-3/4" x 8"</b>		
69957394363	P40	H835
69957394470	P80	A975
69957394472	P120	A975
69957394474	P180	A975
<b>2-3/4" x 16-1/2"</b>		
69957394450	P40	H835
69957394463	P80	A975
69957394464	P120	A975
69957394466	P180	A975

50 STRIPS/PACK



### Multi-Air Hand Blocks

Norton hand blocks are ideal for hand sanding without the dust. The ergonomic handles make them easy to hold and move in any position. Each block comes with a regulator adapter to control air flow and a reducer to allow it to connect to a standard vacuum hose line.

UPC	SIZE
69957396645	2-3/4" x 5"
69957396646	2-3/4" x 8"
69957396648	2-3/4" x 16-1/2"

1 BLOCK/PACK – 4 PACKS/CASE



### Multi-Air Tube and Universal Conical Adapter

The 4-meter hose extension tube with conical adapter is a universal fit for any central or any portable vacuum system.

UPC
07660767979

1 SET/PACK – 1 PACK/CASE



### Multi-Air Shoes

OEMs have self-generating and central-vacuum file machines that can be adapted to the Multi-Air system with shoes.

FOR MODELS:			
UPC	SIZE	HUTCHINS	DYNABRADE
66261191305	2-3/4" x 8"	8623	10404
66261185225	2-3/4" x 16"	4932	4920

10 SHOES/PACK – 1 PACK/CASE



## MORE PRODUCTIVITY MEANS MORE PROFIT



**Saint-Gobain Abrasives, Inc.**  
PO Box 15008, 1 New Bond Street  
Worcester, MA 01615-0008

[www.nortonabrasives.com](http://www.nortonabrasives.com)

#### U.S. CUSTOMER SERVICE:

Phone Toll Free: 1 800 551-4413  
Fax Toll Free: 1 800 551-4416  
Local Phone: (254) 918-2313  
Local Fax: (254) 918-2314

#### CANADA CUSTOMER SERVICE:

Phone Toll Free: 1 800 263-6565  
Fax Toll Free: 1 800 561-9490

PRIMARY SPONSOR



#### FORM #8147

© Saint-Gobain Abrasives, Inc. June 2011  
DryIce, Multi-Air, No-Fil, NorGrip, the Norton logo,  
Norton BlueMag, Norton SG, and SoftTouch are  
registered trademarks of Saint-Gobain Abrasives, Inc.