



INDUSTRIAL ROTARY FUEL PUMP


- » FM Approved, Extra Heavy Duty Industrial Rotary Pump for severe outdoor use in extreme weather conditions
- » Delivers fuels with a head / lift up to 20'
- » Solid cast iron construction, fully CNC machined to close tolerances
- » Pump handle rotates a high quality sintered powder metal 3 Vane Rotor inside a highly finished pumping chamber
- » Graphite Veins are self lubricating & non wearing
- » High quality graphite Seal allow the pump to be used with Class I & Class II flammable & combustible liquids such as Gasoline, Naphtha, Alcohols & other solvents compatible with the pump components
- » Self priming operation with discharge up to 10 GPM
- » Supplied complete with Steel discharge spout with vacuum breaker, Drip Pan with built-in 2" threads and Flame Arrestor, telescopic suction tube with strainer for use with 15-55 gal. drums




5UWH2

FUEL CONTROL NOZZLE – MANUAL

- » For use with Electric Fuel Pumps & gravity feed applications
- » All Metal Construction with the Body, Discharge Spout, Trigger & Guard made from Aluminum
- » Hose Swivel at Inlet for increased maneuverability & convenience in use
- » Manual Control along with a continuous flow switch for unattended dispensing
- » Designed for minimal back pressure & reduction in flow
- » 6-5/16" long Spout
- » For use with Diesel, Kerosene & Gasoline
- » Available in a choice of straight / Curved spout



**Spout Type -
Curved**



**Spout Type -
Straight**

PART #	SPOUT TYPE	INLET THREADS	OUTLET SPOUT DIA.
5URH1	Straight	1" NPT	1"
5URH2	Curved	1" NPT	1"
5URH3	Straight	3/4" NPT	3/4"
5URH4	Curved	3/4" NPT	3/4"
5URH5	Straight	1" NPT	3/4"
5URH6	Curved	1" NPT	3/4"