

Industrial Rotary Drum Pumps


- >Solid, Heavy Duty & Rugged Cast Iron Pumps for use in tough outdoor environments
- >Pump Handle rotates a high quality sintered powder metal 3 Vane Rotor inside a highly finished pumping chamber
- >Graphite Veins are self lubricating & non wearing
- >High Quality graphite Seal allows the pump to be used with a wide variety of fluid
- >Self Priming operation with discharge up to 10 GPM
- >Pumps are supplied complete with 2" Bung, Telescopic Suction Tube with Strainer basket for use with 16-55 gallon drums
- >Available in a Choice of 3 Configurations:

>**4VCR2:** Pump with Steel Discharge Spout for use with Petroleum based fluid, Diesel & Kerosene. Ideal for use with Barrels, drums & tanks for transferring media into smaller containers

>**4VCR3:** Pump with 8' Antistatic Hose, Nozzle & Nozzle Holder for use with Petroleum base fluid, Diesel & Kerosene. Ideal for use with Barrels, Drums & tanks for quickly refueling Diesel powered vehicles or equipments

>**4VCR4:** FM Approved Pump with 8' Anti Static Hose, Nozzle, Nozzle Holder, Flame Arrestor & Vacuum Breaker. For use with Class I & Class II flammable & combustible liquids such as Gasoline, Naphtha, Alcohols & other solvents compatible with the pump components. Ideal for quickly refueling gasoline powered vehicles or equipments

>Also available - Drip pan for the above pumps. Drip pan drains back media into the drum reducing any wastage, spillage etc. It is also used as a base to hold smaller containers during transfer



CAT NR.	DESCRIPTION
4VCR2	With Steel Spout
4VCR3	With Hose & Nozzle
4VCR4	FM Approved, with Hose & Nozzle
4VCR6	Drip pan

