

RB1600 SYSTEM
GREEN REBAR EPOXY**DESCRIPTION AND USES**

Industrial Choice® Green Rebar Epoxy is a high performance epoxy ester aerosol coating designed specifically for the touch up of the rebar. Its fast dry formula protects against corrosion, prevents metal rust stains in concrete and meets the performance requirements of ASTM Standard D3963 (ASTM B117 Salt Fog and ASTM G20 Chloride Permeability).

PRODUCTS

SKU	Description
261937	Green Rebar

PACKAGING

16 fl. oz. container, 12 oz. fill weight

PRODUCT APPLICATION**SURFACE PREPARATION**

ALL SURFACES: Remove all dirt, grease, oil, salt and chemical contaminants by washing the surface with Pure Strength® Cleaner/ Degreaser item #3599402, commercial detergent or other suitable cleaner. Rinse immediately and thoroughly and allow to fully dry. Thoroughly cured, hard or gloss previous coatings which are very smooth may require scuff sanding to maximize adhesion.

STEEL: Hand tool (SSPC-SP-2) or power tool (SSPC-SP-3) clean to remove loose rust, mill scale, and deteriorated previous coatings. For best results, use Industrial Choice Primer on sound rusted or clean metal before the application of the Green Rebar Epoxy.

APPLICATION

Use when temperature is above 50°F (10°C) and humidity is below 85% to ensure proper drying.

Surface temperature must be between 50°F-100°F (10°C-38°C). Protect surrounding surfaces from overspray. Overspray can carry a significant distance. Shake can for one minute after mixing ball is heard. Hold can 10-14" from surface. Apply several light coats a few minutes apart to avoid drips and runs. Recoat within 1 hour or after 24 hours; allow more time in cooler temperatures. Clean valve by turning can upside down and spray for 5 seconds. Some paint will spray out. If clogged, remove tip and clean in thinner. Do not insert any object into can valve opening. Properly discard empty container. Do not burn or place in trash compactor. Empty container can be recycled.

TECHNICAL DATA

RB1600 SYSTEM GREEN REBAR EPOXY

PHYSICAL PROPERTIES

		GREEN REBAR
Resin Type		Epoxy Ester
Pigment Type		Titanium Dioxide, Iron Oxides
Solvents		Acetone, Butyl Acetate, Xylene
MIR		1.40 Max
Fill Weight		12 ounces
Recommended Dry Film Thickness (DFT) Per Coat		1.0-2.0 mils (25-50μ)
Wet Film to Achieve DFT(unthinned material)		4.0-5.0 mils (100-125μ)
Practical Coverage at Recommended DFT (assumes 15% material loss)		8-9 sq.ft./can
Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity	Touch	15 minutes
	Recoat	Within 1 hour or after 1 week
Dry Heat Resistance		200°F (93°C)
Shelf Life		5 years
Safety Information	Contains	Acetone, Xylene, and Toluene; Lead-free
	Warning!	THIS PRODUCT CONTAINS A CHEMICAL KNOWN TO THE STATE OF CALIFORNIA TO CAUSE CANCER AND BIRTH DEFECTS AND OTHER REPRODUCTIVE HARM. DANGER! EXTREMELY FLAMMABLE. MAY CAUSE FLASH FIRE. CONTENTS UNDER PRESSURE. VAPOR HARMFUL. FOR INDUSTRIAL OR COMMERCIAL USE ONLY. SEE THE PRODUCT MATERIAL SAFETY DAT SHEET (MSDS) AND LABEL WARNINGS FOR ADDITIONAL SAFETY INFORMATION.

Calculated values are shown and may vary slightly from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.