



IDENTIFICATION
GROOVE

\varnothing 1.000^{+0.003}_{-0.000}
BORE SIZE



1/4-28 UNF-3A x 5/8"
STAINLESS STEEL, SPEC.:
(ASTM F837 - 13e1)
CLAMP SCREW

\varnothing 2-1/16"
CLEARANCE



NOTES:

1. APPROX. WEIGHT: 3.3 oz.
2. TEMPERATURE RATING: -40° to +220°F
3. MATERIAL / FINISH: Stainless Steel, ASTM A582, Plain
4. APPLICATION / FEATURES:
 - Greater Axial Holding Power than Set Screw Collars.
 - Effective on Hard & Soft Shafts, Fully Engages the Shaft w/out Marring

COMPONENT		Shaft Collar, Industry Standard	
<h1>29NV79</h1>		UNIT	
		INCH	
Stainless Steel, One-Piece Clamp Type 1/2" W x 1-3/4" D x 1" Bore		SHEET	
		1 of 1	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.58