

STANLEY

PROTO[®]

QUICK RELEASE RATCHETS

- Small, pear head design for access in tight hard to reach work areas
- 45 Tooth gear, 8 degree swing articulation
- Low profile quick release button for access in restricted areas.
- Low profile reversing lever design for quick, one-handed operation.
- Patented sealed head design helps prevent debris from entering the ratchet mechanism reducing wear. Also, helps to keep lubrication contained within the components.
- Contoured, ergonomically-designed handle for comfort. Knurled bands allow for increased grip and slip resistance
- Full polished handle, easy to clean
- Double nickel chrome plated for enhanced corrosion protection meeting aerospace requirements
- ASME B107.10
- Field repairable



J5249XLQR



Product SKU No.	Drive Size	O/A Length	UPC/UIC	Weight (lbs.)	ASME Spec.	Repair Kit
J4749XLQR	1/4"	6-11/16"	662679006068	0.25 lbs.	ASME B107.10	J4749XLORRK
J5249XLQR	3/8"	8-1/2"	662679006075	0.86 lbs.	ASME B107.10	J5249XLORRK
J5449XLQR	1/2"	10-1/2"	662679033576	1.72 lbs.	ASME B107.10	J5449XLORRK
J5450XLQR	1/2"	15"	662679006082	2.18 lbs.	ASME B107.10	J5449XLORRK

©2009 THE STANLEY WORKS

2195 East View Parkway, Suite 103 Conyers, GA 30013
 www.stanleyproto.com Customer Service: 1-800-800-TOOL
 WARNING: Work Safely With Tools Wear Safety Goggles.

P20978