

STANLEY

PROTO[®]

RATCHET

- Small pear head design for access in tight hard to reach work areas.
- 45 tooth gear provides balance between 8 degree articulation angle and high torque carrying capacity.
- Sealed design helps prevent debris from entering ratchet mechanism reducing wear. Also, helps to keep lubrication contained within the components. *Patent pending design.*
- Low profile reversing lever design for quick, one hand operation.
- Available in three drive sizes: 1/4", 3/8" and 1/2"
- Contoured, ergonomically-designed handle for comfort. Knurled bands allow for increased grip and slip resistance.
- Available in standard and long-length handles in both 3/8" and 1/2" drive sizes.
- Double nickel chrome plated for enhanced corrosion protection.
- Full polish finish for superior comfort and easy clean up. Black oxide finishes are also available.
- Field repairable
- Limited Lifetime Warranty
- Manufactured to ASME B107.10M specifications



SKUS	Drive Size	Description	Finish	Length	Weight lbs.	Repair Kit Number
J4749XL	1/4"	Standard Length	Full-Polished	5.7"	0.260	J4749XLRK
J4749XLBL	1/4"	Standard Length	Black Oxide	5.7"	0.260	J4749XLRK
J5249XL	3/8"	Standard Length	Full-Polished	8.5"	0.875	J5249XLRK
J5249XLBL	3/8"	Standard Length	Black Oxide	8.5"	0.875	J5249XLRK
J5250XL	3/8"	Long Handle	Full-Polished	11"	1.000	J5249XLRK
J5250XLBL	3/8"	Long Handle	Black Oxide	11"	1.000	J5249XLRK
J5449XL	1/2"	Standard Length	Full-Polished	10.5"	1.750	J5449XLRK
J5449XLBL	1/2"	Standard Length	Black Oxide	10.5"	1.750	J5449XLRK
J5450XL	1/2"	Long Handle	Full-Polished	15"	2.188	J5449XLRK
J5450XLBL	1/2"	Long Handle	Black Oxide	15"	2.188	J5449XLRK

©2005 THE STANLEY WORKS

2195 East View Parkway, Suite 103 Conyers, GA 30013
www.stanleyproto.com Customer Service: 1-800-800-TOOL

WARNING: Work Safely With Tools Wear Safety Goggles.

T20520 11/05