








Speed Reducer Type	Indirect Drive	Max. Output Torque (in-lb)	285
Shaft Orientation	Right Angle	Overhung Load (lb.)	600
NEMA/IEC Frame	N/A	Nominal Output RPM	30
Standards	AGMA	Number of Stages	1
Seal Type	Double Lip	Max. Input HP	0.3
Rotation	Forward/Reversible	Nominal Ratio	58:1
Duty	Standard	Input RPM	1750

NOTES:

1. GEAR TYPE: Worm
2. BEARINGS: Tapered Roller
3. FINISH: Powdered Epoxy Paint
4. HOUSING MATERIAL: Cast Iron
5. WORM GEAR MATERIAL: Bronze
6. PINION MATERIAL: Hardened Steel
7. SHAFT OUTPUT/TYPE: Single/Solid
8. LUBRICATION: Klubersynth UH1 6-460
9. GEAR MATERIAL: Hardened and Ground Steel
10. OUTPUT TORQUE (in.-lb.)
 - @ 1/6 HP 96
 - @ 1/4 HP 128
 - @ 1/3 HP 193
 - @ 1/2 HP 285

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.38

COMPONENT	Speed Reducer		
2Z306	UNIT		
	INCH		
	SHEET		
Speed Reducer, Indirect Drive, 58:1	1 of 1		