





|                 |                  |                       |                        |
|-----------------|------------------|-----------------------|------------------------|
| Series          | Parker 60 Series | Coupler Body Size     | 3/4"                   |
| Valve Design    | Poppet           | Coupler Flow Rate     | 28.0 gpm               |
| Seal Material   | Buna             | Locking Mechanism     | Ball                   |
| Max. Pressure   | 1500 psi         | Coupler Thread Size   | 3/4"-14                |
| Coupler Finish  | Plain            | Coupler Body Material | 303 Stainless Steel    |
| Connection Type | FNPT             | Quick Coupler Type    | Hydraulic Coupler Body |



**NOTES:**

- ITEM: Hydraulic Coupler Body
- STANDARDS: ISO 7241-1 Series B
- PARKER INTERCHANGE: SH6-62
- BEARING MATERIAL: Stainless Steel
- SLEEVE MATERIAL: 303 Stainless Steel
- OPERATING TEMP. RANGE: -40° to 250°F
- FOR USE WITH: ISO 7241-1 Series B Nipple
- COUPLER INTERCHANGE TYPE: ISO 7241-1 Series B

|                  |                          |
|------------------|--------------------------|
| <b>COMPONENT</b> | Hydraulic Quick Couplers |
|------------------|--------------------------|



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** 0.79

|               |              |
|---------------|--------------|
| <b>31A870</b> | <b>UNIT</b>  |
|               | INCH         |
|               | <b>SHEET</b> |
|               | 1 of 1       |

Coupler Body,3/4-14,3/4 In. Body,303 SS