



Series	FF	Max. Pressure	5075 psi
Shut Off	Flat Face	Sleeve Material	Zinc Plated Steel
Standards	ISO 16028	Connection Type	FSAE
Seal Material	Buna	Coupler Flow Rate	7.2 gpm
Valve Design	Tubular	Locking Mechanism	Standard Sleeve Lock
Bearing Material	Stainless Steel	Coupler Thread Size	9/16"-18

#### NOTES:

1. SEAL TYPE: Buna N
2. COUPLER BODY SIZE: 1/2"
3. ITEM: Hydraulic Coupler Nipple
4. COUPLER FINISH: Clear Chromate
5. PARKER INTERCHANGE: FEM252-6FO
6. COUPLER INTERCHANGE TYPE: HTMA
7. OPERATING TEMP. RANGE: -4° to 212°F
8. COUPLER BODY MATERIAL: Zinc Plated Steel
9. FOR USE WITH: Mfr. No. 6FFS25, 6FFS56UN
10. QUICK COUPLER TYPE: Hydraulic Coupler Nipple

COMPONENT	Hydraulic Quick Couplers		
33M284	UNIT		
	INCH		
	SHEET		
	1 of 1		

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.71

Nipple, 9/16-18, Body, Zinc Plated Steel