





|                  |                 |                     |                      |
|------------------|-----------------|---------------------|----------------------|
| Series           | FF              | Max. Pressure       | 5075 psi             |
| Shut Off         | Flat Face       | Sleeve Material     | Zinc Plated Steel    |
| Standards        | ISO 16028       | Connection Type     | FSAE                 |
| Seal Material    | Buna            | Coupler Flow Rate   | 6.0 gpm              |
| Valve Design     | Tubular         | Locking Mechanism   | Standard Sleeve Lock |
| Bearing Material | Stainless Steel | Coupler Thread Size | 3/4"-16              |

#### NOTES:

1. COUPLER BODY SIZE: 3/8"
2. ITEM: Hydraulic Coupler Nipple
3. COUPLER FINISH: Clear Chromate
4. PARKER INTERCHANGE: FEM372-8FO
5. COUPLER INTERCHANGE TYPE: HTMA
6. OPERATING TEMP. RANGE: -4° to 212°F
7. COUPLER BODY MATERIAL: Zinc Plated Steel
8. FOR USE WITH: Mfr. No. 10FFS37, 10FFS75UN
9. QUICK COUPLER TYPE: Hydraulic Coupler Nipple

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** 1.34

| COMPONENT                                                | Hydraulic Quick Couplers |  |  |
|----------------------------------------------------------|--------------------------|--|--|
| <b>33M293</b><br><br>Nipple, 3/4-16, 3/8 In. Body, Steel | UNIT                     |  |  |
|                                                          | INCH                     |  |  |
|                                                          | SHEET                    |  |  |
|                                                          | 1 of 1                   |  |  |