

 **CRESCENT**

 **CRESCENT**
Wiss

 **CRESCENT**
Lufkin

 **CRESCENT**
NICHOLSON

 **CRESCENT**
H.K. PORTER

 **CRESCENT**
JOBBOX

 **CRESCENT**
APEX



Product Supplement
Featuring new and top selling items

Trusted by the Trades.



CONTENTS

Crescent Hand Tools

Wide Jaw Adjustable Wrenches 6

Adjustable Wrenches 7

Pipe Wrenches 8

X6/X10 Wrenches 10

Wrench Sets..... 12

Hex Keys..... 12

Pliers 14

Hammers 16

Screwdrivers 16

Tool Sets 17

Squares & Layout 18

Tool Bags..... 20

Crescent JOBOX On-Site Storage

Mesh Cabinets..... 22

Safety Cabinets..... 24

Mobile Field Office 28

Chests 30

Piano Boxes..... 32

Two-Door Cabinet 34

Crescent Lufkin Tape Measures

Shockforce Tapes 36

Control Series Tapes 38

Power Tapes 39

Long Construction Tapes..... 40

Measuring Wheels..... 41

Crescent Wiss Cutting Tools

Aviation Snips..... 42

Knives..... 44

HVAC Tools..... 44

Tradesman Shears..... 46

Crescent HK Porter Cutting Tools

Bolt Cutters 48

Rebar Cutters/Benders..... 49

Strap Cutters 50

Ratcheting Cutters..... 51

Crescent Nicholson Files 52

Crescent APEX Bits 54

WHY Crescent?

Crescent hand tools have been an essential part of professional toolboxes for over a century. Why? Because at Crescent, we make products for people who depend on their tools to make a living. People who need tools that will stand up to the tough conditions found on every jobsite. People who recognize tools that deliver meaningful performance. Like a tape measure with an industry-leading 14 feet of standout. Or made in USA snips with ten times the cut life of anything else on the market. That's quality to get the job done right and superior performance to save time. Crescent offers thousands of tools, each one made to consistently deliver dependable, high quality results. Crescent. Trusted by the Trades.



Karl Peterson founds the Crescent Tool Company and introduces his revolutionary Crescent® Adjustable Wrench the following year. The unique tool is an instant success and, along with the Ford Model T, soon dominates the market.

1907



Newspapers around the world carry a report that a young aviator named Charles Lindbergh has made the first solo transatlantic flight with a scant cargo of "gasoline, sandwiches, a bottle of water, and a Crescent® wrench and pliers."

1927



At the request of the U.S. Army Air Corps, Crescent® develops Crestoloy steel alloy to make its adjustable wrenches lighter and stronger. By 1938, Crescent® is manufacturing thousands of Crestoloy tools for the Air Corps. When the country enters World War II, the plant operates around-the-clock with all output going to the war effort.

1930



Crescent® vans begin traveling the country, visiting distributors and showing new products. This is a tradition that continues to this day.

1964

1965

The media reports that Crescent® tools are aboard the first manned Gemini space flight.



1997

The Crescent® adjustable wrench receives its first major redesign in over 50 years, with a wider, more comfortable handle and increased jaw opening capacity over the entire line.



2017

To easier identify the Crescent®-quality tools, the line expands to include four iconic brands: Wiss® shears and snips, Lufkin® measuring products, Nicholson® files and saws and HK Porter® heavy-duty cutting tools. Together, Crescent® Tools is formed and provides professional tradesman thousands of jobsite solutions all under one unified brand.



2019

Crescent Lufkin® introduces the revolutionary Shockforce™ and Shockforce Nite Eye™ tape measures, both with 14 feet of standout and a compact design durable enough to survive a 100-foot drop.



2019

JOBBOX® on-site, and truck storage products are added to the Crescent® family of tools. The new line of UL Listed Flammable Liquid Storage Cabinets is then introduced, providing users with the ultimate level of confidence.



2019

The Crescent Mobile Showroom begins touring the country, stopping at construction jobsites and distributor locations bringing contests, sales promotions, and hands-on opportunities for end users to try out the latest Crescent® Tools products.



2019

Crescent Wiss® introduces its Next Generation Aviation Snips. The new snips last 60% longer and require 20% less force to cut on average compared to the same snips from just five years earlier.

Crescent APEX® industrial bits are added to the Crescent® family of tools.



2019

Crescent® introduces new Wide Jaw Adjustable Wrenches that deliver next level strength performance with the same strength and jaw capacity as next size longer competitive wrenches, resulting in less weight and bulk in user toolboxes.



Crescent Wide Jaw Adjustable Wrenches

These wrenches really punch above their weight when it comes to strength and jaw capacity. They open wide to work on fasteners that would need the next larger size standard adjustable. For example, a 10-inch Crescent Wide Jaw has the same strength and jaw capacity as a 12-inch standard adjustable, so they save space and weight in your toolbox. Lighten your load with these new tools from Crescent ... the original name in adjustable wrenches.

Exceeds ASME Requirements
Meets performance standards of the next larger size

Black Phosphate and Lacquer Finish
Resists rust and corrosion

Serrations on Jaws
Gives up to 4X more torque than traditional adjustables

Larger Knurl
For easier adjustment and tighter jaw fit, won't bind up

Laser Etched Scale
SAE and Metric, allows easy determination of fastener size

Wider Jaw Opening
Allows use with a greater range of fastener sizes than traditional adjustables.

ATWJ210VS

4X MORE TORQUE

SUPER DUTY

KNURL

EXTRA WIDE JAW

NEXT LEVEL STRENGTH

Part No	Description	Max Opening	Size Designation	Packaging
ATWJ26VS	6" Wide Jaw Adjustable Wrench	1-1/8"/29mm	SAE/Metric	Card
ATWJ28VS	8" Wide Jaw Adjustable Wrench	1-5/16"/33mm	SAE/Metric	Card
ATWJ210VS	10" Wide Jaw Adjustable Wrench	1-1/2"/39mm	SAE/Metric	Card
ATWJ212VS	12" Wide Jaw Adjustable Wrench	1-3/4"/44mm	SAE/Metric	Card
ATWJ2610VS	6" & 10" Wide Jaw Adjustable Wrench Set	1-1/8"/29mm, 1-1/2"/39mm	SAE/Metric	Card



Crescent Adjustable Wrenches

Part No	Description	Max Opening	Packaging
AC24CVS	4" Chrome with Cushion Grip	1/2"/13mm	Card
AT24VS	4" Black Phosphate	1/2"/13mm	Card
AC24VS	4" Chrome	1/2"/13mm	Card
AC26CVS	6" Chrome with Cushion Grip	15/16"/24mm	Card
AC26VS	6" Chrome	15/16"/24mm	Card
AT26VS	6" Black Phosphate	15/16"/24mm	Card
AC28VS	8" Chrome	1-1/8"/29mm	Card
AC28CVS	8" Chrome with Cushion Grip	1-1/8"/29mm	Card
AT28VS	8" Black Phosphate	1-1/8"/29mm	Card
AC210VS	10" Chrome	1-5/16"/33mm	Card
AC210CVS	10" Chrome with Cushion Grip	1-5/16"/33mm	Card
AT210SPUD	10" OAL Construction, Sensormatic	1-5/16"/33mm	Card
AT210VS	10" Black Phosphate	1-5/16"/33mm	Card
AC212VS	12" Chrome	1-1/2"/39mm	Card
AT212VS	12" Black Phosphate	1-1/2"/39mm	Card
AC212CVS	12" Chrome with Cushion Grip	1-1/2"/39mm	Card
AC215VS	15" Chrome	1-11/16"/43 mm	Hang Tag
AT215SPUD	16" Construction	1-1/2"/39mm	Card
AC218VS	18" Chrome	2-1/16"/52mm	Hang Tag
AC224VS	24" Chrome	2-7/16"/62mm	Hang Tag
AC2610CVS	6" & 10" Chrome with Cushion Grip Set	15/16"/24mm, 1-5/16"/33mm	Card
AT2610CVS	6" & 10" Black Phosphate with Cushion Grip Set	15/16"/24mm, 1-5/16"/33mm	Card
AC2610VS	2 Pc. Adjustable Set	15/16"/24mm, 1-5/16"/33mm	Card
AC26810CV	6", 8", 10", Chrome with Cushion Grip Set	15/16"/24mm, 1-1/8"/29mm, 1-5/16"/33mm	Card
AC3PC	6", 8", 10", Chrome Set	15/16"/24mm, 1-1/8"/29mm , 1-5/16"/33mm	Card

Crescent Pipe Wrenches

Our new Crescent Pipe Wrenches have been redesigned from the ground up to be lighter, quicker to adjust, and more comfortable to use. But even more, they've been designed to deliver the most powerful pipe grip ever with our new straight wrenches offering larger bite surfaces and exclusive K9™ 30-degree angle access jaws that give you massive turning power, even in the tightest, most restricted situations.

Straight Pipe Wrenches come in both cast aluminum and cast iron. Aluminum models are more than 40% lighter than typical cast iron wrenches with thicker cross-sections in high-stress areas for exceptional strength. Our cast iron wrenches have also been optimized for strength, weighing up to 10% less than competitive products.

* COMING SOON! Available early 2020



**RAPID
ADJUST
JAWS**
2X FASTER


**MORE THAN
40%
LIGHTER**
THAN CAST IRON

**ONE
HAND
SELF
ADJUST**

**2X
GRIPPING
POWER**

Our Self-Adjusting Pipe Wrenches offer compact size, light weight, and a jaw design that locks open for easier placement onto pipes in tight spots.

* COMING SOON! Available early 2020



*Aluminum models

Part No	Description	Length	Pipe Size Max	Total Weight	Packaging
CPW12	12" Self Adjusting, Grip	12"	3/8-1 in	1.3 lbs.	Card
CPW12S	12" Self Adjusting, Steel Handle	12"	3/8-1 in	1.3 lbs.	Card
CPW16S	16" Self Adjusting, Steel Handle	16"	7/8-2 in	3.1 lbs.	Card
CAPW10S	10" Aluminum, Slim Jaw	10"	1-1/2 in	.98 lbs.	Card
CAPW14	14" Aluminum - Angle Access	14"	2 in	2.14 lbs.	Card
CAPW14L	14" Aluminum, Long Handle	14L"	2 in	2.63 lbs.	Card
CAPW18	18" Aluminum - Angle Access	18"	2-1/2 in	3.37 lbs.	Card
CAPW24	24" Aluminum	24"	3 in	5 lbs.	Card
CIPW10S	10" Cast Iron, Slim Jaw	10"	1-1/2 in	1.74 lbs.	Card
CIPW14	14" Cast Iron - Angle Access	14"	2 in	3.51 lbs.	Card
CIPW18	18" Cast Iron - Angle Access	18"	2-1/2 in	5.69 lbs.	Card





- Off-corner loading technology on the box-end reduces fastener rounding
- Extra long handle
- Corrosion resistant finish

CCWS98M

CCWS98S

Crescent X10 12-Point Wrenches

Part No	Description	Piece Count	Size Designation	Packaging
CCWS98M	9 Pc. X10 12 Point Long Pattern Combination Set	9	Metric	Reusable V-Rack
CCWS98S	9 Pc. X10 12 Point Long Pattern Combination Set	9	SAE	Reusable V-Rack
CCWS38B	20 Pc. X10 3/8" Drive 6 Point Standard Set	20	SAE/Metric	Reusable Rack





CX6RWS7

- Innovative stepped box ends deliver improved access in low-clearance areas
- 5-degree ratcheting arc lets you turn restricted fasteners
- Smooth profile handle allows you to comfortably apply more torque to the fastener
- Versatile — moves quickly between 6 styles of fasteners in 4 common sizes
- Superior strength and resistance to corrosion

Crescent X6 Spline Wrenches

Part No	Description	Piece Count	Size Designation	Packaging
CX6DBM2	2 Pc. X6™ 4-in-1 Black Oxide Spline Ratcheting Set	2	Metric	Box
CX6DMS2	2 Pc. X6™ 4-in-1 Black Oxide Spline Ratcheting Set	2	SAE	Box
CX6RWS7	7 Pc. X6™ Black Oxide Spline Open End Ratcheting Combination Set	7	SAE	Box
CX6RWM7	7 Pc. X6™ Black Oxide Spline Open End Ratcheting Combination Set	7	Metric	Box
CX6PT20	20 Pc. 3/8" Drive Pass-Thru® X6™ Standard Spline Set	20	SAE/Metric	Reusable Rack



Seven Legendary Tool Names Under One Iconic Brand















Trusted by the Trades.

Since 1907, tradesmen have trusted Crescent for tools they can depend on to get the job done. Now, united with six other great brands, Crescent has thousands of quality products to choose from. Crescent ... the new power in hand tools.

See the entire line of Crescent brand products now at www.crescenttool.com





CCWS5

- Off-corner loading technology on the box-end reduces fastener rounding
- Size stamped markings for easy identification
- Full polish chrome finish that easily wipes clean of oil and dirt

Crescent Wrench Sets

Part No	Description	Piece Count	Size Designation	Packaging
CCWS2	10 Pc. 12 Point SAE Combination Set	10	SAE	Reusable Rack
CCWS3	10 Pc. 12 Point Metric Combination Set	10	Metric	Reusable Rack
CCWS4	14 Pc. 12 Point SAE Combination Set with Tool Roll	14	SAE	Box
CCWS5	15 Pc. 12 Point Metric Combination Set with Tool Roll	15	Metric	Box



CCWS9BM

CCWS9BM

CCWS9BM

- Dual material comfort grip
- Size markings for each key
- Measurement type clearly printed for easy recognition
- High strength alloy steel
- Versatile range of common sizes

Crescent Hex Keys

Part No	Description	Contents	Packaging
CHK3PC	3 Pc. Folding SAE/Metric/Torx® Dual Material Key Set	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, T9, T10, T15, T20, T25, T27, T30, T40	Card
CHKFM8	3 Pc. Folding Metric Dual Material Key Set	1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm	Card
CHKFT8	3 Pc. Folding Torx® Dual Material Key Set	T9, T10, T15, T20, T25, T27, T30, T40	Card
CHKFSA	3 Pc. Folding SAE Dual Material Key Set	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"	Card



Introducing Next Generation Aviation Snips. Made in the USA to earn the trust of a new generation.

We combine the shape consistency of investment casting with our proprietary serration process to produce blades that cut up to 8 miles of steel...more metal than any other snips.



An American Icon. Improved.

Continuous improvement means never being satisfied. That's why these new Next Generation snips last 60% longer and require 20% less force to cut on average compared to our snips from just five years ago. It's why Crescent Wiss snips are the undisputed choice of sheet metal professionals.

*Based on maximum performance.

© 2019 Apex Tool Group, LLC



Trusted by the Trades.

See the entire line of Crescent brand products now at www.crescenttool.com



Crescent Tongue and Groove Pliers with Grip Zone™

These redesigned pliers offer improved jaw geometry and a unique tooth design for better grip and more torque with less effort. A rubber grip area integrated into the handles holds chrome pipes and fixtures without marring. “V” jaws allow for firmer grip on various shapes, while alloy steel construction with induction hardened teeth maximizes durability.

Induction Hardened Teeth
Maximizes durability

"V" Jaws
Allow for firmer grip on various shapes

Unique Tooth Design
Better grip — increases torque with less effort

Alloy Steel Construction
Maximizes durability

Comfort Grip Handle

Black Oxide Finish
Resists corrosion

Non-Marring Pipe Grip Area
Integrated into handle

GRIPZONE™

RT412SGVN

Part No	Description	Jaw Capacity	Jaw Type	Packaging
RT412SGVN	12" Grip Zone Tongue & Groove Plier	3"	V-Jaw	Carded
RT410SGVN	10" Grip Zone Tongue & Groove Plier	2"	V-Jaw	Carded
RT400SGSET2	10" and 12" Tongue and Groove 2 Pc. Plier Set	2" - 3"	V-Jaw	Carded

MORE

JAW POSITIONS

MAX GRIP

DEEPER JAWS

NON MARRING



RT27CVN

- 6, 8 or 10 jaw positions offer more flexibility and more comfort
- Increased capacity: 1-5/16" to 4-1/2"
- Black phosphate finish for ultimate corrosion resistance
- Unique tooth design allows for better grip — increases torque with less effort

Crescent Tongue and Groove Pliers

Part No	Description	Jaw Capacity	Jaw Type	Packaging
RT27CVN	7" Straight Jaw Tongue and Groove Plier, Black Phosphate	1-1/2"	Straight Jaw	Carded
RT210CVN	10" Straight Jaw Tongue and Groove Plier, Black Phosphate	1-5/8"	Straight Jaw	Carded
RT212CVN	12" Straight Jaw Tongue and Groove Plier, Black Phosphate	2-5/8"	Straight Jaw	Carded
RT216CVN	16" Straight Jaw Tongue and Groove Plier, Black Phosphate	4-1/2"	Straight Jaw	Carded
RT410CVN	10" V-Jaw Tongue and Groove Plier, Black Phosphate	1-13/16"	V-Jaw	Carded
RT412CVN	12" V-Jaw Tongue and Groove Plier, Black Phosphate	3"	V-Jaw	Carded



C10CVN

- Angled teeth provide more torque with less effort
- Wire cutter featured on curved jaw and long nose styles
- Deep-rib knurl pattern is easier to grip and turn
- Hex key recess can be used for tightening or loosening
- Cushioned release lever is more comfortable to use

Crescent Locking Pliers

Part No	Description	Jaw Capacity	Jaw Type	Packaging
C10CVN	10" Locking Plier	1-7/8"	Curved Jaw	Carded
C10SVN	10" Straight Jaw Locking Plier	1-7/8"	Straight Jaw	Carded
CLP5SETN	5 Pc. Locking Plier Set	—	—	Carded
C6NVN	6" Long Nose Locking Plier	2-1/4"	Straight Jaw	Carded
C9NVN	9" Long Nose Locking Plier	2-7/8"	Straight Jaw	Carded
C7CVN	7" Curved Jaw Locking Plier	1-5/8"	Curved Jaw	Carded
C6CCVN	6" Locking C Clamp with Regular Tips	2"	Regular Tips	Carded
C7SVN	7" Straight Jaw Locking Plier	1-5/8"	Straight Jaw	Carded
C5CVN	5" Curved Jaw Locking Plier	1-1/4"	Curved Jaw	Carded



CCA5428

- Dual material grips for added comfort and durability
- Forged steel body for strength and durability
- Machined cross-check jaw pattern for gripping
- Unique pivot action design requires 40% less force to cut

Crescent Pliers

Part No	Description	Jaw Capacity	Jaw Type	Packaging
PSX200C	X2 Series Long Nose Plier	4"	Straight Jaw	Carded
CCA5428	8" Diagonal Pivot Pro® Plier with Compound Action	5/8"	—	Carded
CCA20509	9" Linesman Pivot Pro® Plier with Compound Action	1-5/16"	—	Carded
H26VN	6 1/2" Combination Slip Joint Plier	1"	Curved Jaw	Carded
H28VN	8" Combination Slip Joint Plier	1"	Curved Jaw	Carded



CINDEX18

- Indexing claw adjusts to four positions to provide the best leverage
- Forged carbon steel handle and claw for maximum strength
- TPR grip provides comfort and prevents slippage
- Magnetic nail starter holds nail securely for quick, one handed nail starting

Crescent Hammers

Part No	Description	Handle Material	Product Weight	Packaging
CINDEX18	18 oz. Indexing Claw Hammer	Steel	18 oz.	Card
11419C	16 oz. Fiberglass Hammer	Fiberglass	16 oz.	Card
11418C	20 oz. Fiberglass Hammer	Fiberglass	20 oz.	Card



CGS4PCSET

- Diamond tips give up to four times the grip of non-coated tips
- Thermoplastic rubber molded allows users to apply up to 20% more torque
- Black oxide blades with laser-etched markings allow for easy identification

Crescent Screwdrivers

Part Number	Description	Piece Count	Packaging
CGPS8PCSET	8 Pc. Co-Molded, Diamond-Tipped Screwdriver Set	8	Card
CGS4PCSET	4 Pc. Co-Molded, Diamond-Tipped Screwdriver Set	4	Card



CTK170MPN

- Carefully selected assortment of hand tools needed for most industrial, mechanical, and consumer applications
- Sturdy blow mold case with steel hinges and 4 latches to keep tools organized and secure
- Kit includes longer wrenches with narrower heads, wrenches and pliers, Torx bit sockets, acetate screwdrivers and a ratchet with 10% longer beam and smaller teardrop head
- Set includes 1/4", 3/8" & 1/2" drive tools [SAE & Metric]

Crescent Mechanic Tool Sets

Part No	Description	Piece Count	Size Designation	Packaging
CTK170MPN	170 Pc. General Purpose Set	170	SAE/Metric	Blow Mold Case
CTK148MPN	148 Pc. General Purpose Set	148	SAE/Metric	Blow Mold Case
CTK128MP2N	128 Pc. Mechanics Tool Set, Closed	128	SAE/Metric	Blow Mold Case
CTK142	142 Pc. Mechanics Tool Set	142	SAE/Metric	Blow Mold Case
CTK121	121 Pc. Mechanics Tool Set	121	SAE/Metric	Blow Mold Case
CTK70MPN	70 Pc. Mechanics Tool Set, Closed	70	SAE/Metric	Blow Mold Case
CTK30SETN	30 Pc. Mechanics Tool Set, 3/8" Drive	30	SAE/Metric	Blow Mold Case
CTK21SAEN	21 Pc. Mechanics Tool Set, 3/4" Drive	21	SAE	Blow Mold Case
CTK14SAEN	14 Pc. Mechanics Tool Set, 3/4" Drive	14	SAE	Blow Mold Case
CTK84CMPN	84 Pc. 1/4" & 3/8" Drive Socket Wrench Set, Standard & Deep	84	SAE/Metric	Blow Mold Case
CSWS12N	12 Pc. 1/2" Drive Socket Wrench Set	12	SAE/Metric	Reusable Rack
CSWS10N	52 Pc. 3/8" Drive Socket Wrench Set, Standard & Deep	52	SAE/Metric	Blow Mold Case
CSWS9N	27 Pc. 3/8" Drive Socket Wrench Set, Standard & Deep	27	Metric	Blow Mold Case
CSWS8N	25 Pc. 3/8" Drive Socket Wrench Set, Standard & Deep	25	SAE	Blow Mold Case
CSWS7N	20 Pc. 3/8" Drive Socket Wrench Set, Standard	20	SAE/Metric	Reusable Rack
CSWS1N	20 Pc. 1/4" Drive Socket Wrench Set	20	SAE/Metric	Reusable Rack
CBSS0N	7 Pc. 3/8" Drive Hex Bit Socket Set	7	SAE	Reusable Socket Rack
CBSS1N	7 Pc. 3/8" Drive Hex Bit Socket Set	7	Metric	Reusable Socket Rack

Crescent Ex6 Layout Square

An original in its category, Crescent's Ex6 layout square delivers 2-in-1 capabilities, making woodworking and framing simpler. The Ex6 eliminates the need to carry a 7-in and 12-in square and acts as a continuous edge for scribing and marking large scale lumber. Laser-etched markings add another level of efficiency, increasing visibility and significantly reducing signs of wear and tear. When you've finished a task, the tool conveniently folds to fit comfortably in a pocket or work pouch. A practical locking mechanism holds the foldout extension securely for transport. With all the elements of a standard layout square and high-performing additions, the Ex6 is sure to be an essential tool that trades professionals take wherever they go.

Quick Access Thumb Lock
For releasing the swing arm and locking it back in place after use




Solid Aluminum Construction
With laser-etched markings for added protection against harsh environmental conditions and product abuse
Aluminum finish reduces heat retention while working on roofs or in other extreme conditions

Patent-Pending Foldout Extension
Creates a 2-in-1 tool and eliminates the need to carry a 7-in and 12-in square
Also acts as continuous edge for scribing and marking large scale lumber

6 More Inches!

Ex6 in closed position



Item No	Description	Product Package Dimensions	Product Weight	Inner Pack Qty	Case Pack Qty
L06CS	6" Combination Square	6.02"L x 3.39"W x 0.51"H	0.24 lbs.	5	60
L12CS	12" Combination Square	12.01"L x 4.8"W x 0.75"H	0.67 lbs.	5	60
L0812US	8" x 12" Hi-Viz Steel Utility Square	12.01"L x 7.99"W x 0.09"H	0.65 lbs.	6	48
L1624CS	16" x 24" Hi-Viz Steel Carpenter Square	23.94"L x 15.98"W x 0.12"H	1.65 lbs.	6	24
L1624RS	16" x 24" Hi-Viz Aluminum Rafter Square	23.94"L x 15.98"W x 0.12"H	0.78 lbs.	6	60
L48DS	48" Drywall Square	49.61"L x 22.05"W x 0.65"H	2.38 lbs.	-	10
LSSP6	7" Ex6 Aluminum Casting Square	11.42"L x 9.87"W x 1.08"H	0.73 lbs.	6	36

Crescent Tradesman Tool Bags

Introducing the new line of Crescent Tool Bags. Made for strength. Made to last. Made for the long haul. Superior tool organization combined with the quickest and easiest access. These bags are made to take the drops, drags, hits and misses that are just part of life on every jobsite.

Tubular Steel Handle
With quad-riveted, high-durability comfort grip

Sturdy D-Ring
Attachment points

Bright Orange Interiors
Make it easier to see tools in low light conditions and dark jobsites

Tear-Resistant 1680D Ballistic Material
For maximum durability

Tape Measure Clip
For added convenience

Center Panels
Separate tools and allow for additional storage sleeves

Open-Bottom Inner Sleeves
Keep small tools and bits from being lost at the bottom of pockets

Rugged Polypropylene Base
Built to protect your tools from impact and moisture

YKK Zippers
Allow secure closure and easy access

Magnetic-Closure Pocket
For easy access to keys, cell phone, and other frequently used items

Zippered Interior Mesh Pockets
For quick view of contents

Large Adjustable Front Pocket
For easy access to bulky items like power cords

Tear-Resistant 1680D Ballistic Material
For maximum durability

Rugged Polypropylene Base
Built to protect your tools from impact and moisture

CLICK HERE

On Closed-Style Bags:
PALS-Style Webbing Allows fast and easy access to frequently used tools

MAGNETIC POCKET

CENTER DIVIDE

INCREASED ORGANIZATION

STRAIGHT POCKET

EASY ACCESS



Item No	Description	Pockets Outside	Pockets Inside	PALS	Product Dimensions	Product Weight
CTB1450	14" Closed Bag	3	29	13	14"L x 8.2"W x 14.5"H	5.2 lbs.
CTB1410	14" Open Bag	8	17	0	14"L x 9.6"W x 14.5"H	5.5 lbs.
CTB1750	17" Closed Bag	3	29	13	17"L x 9.5"W x 16.7"H	6.5 lbs.
CTB1710	17" Open Bag	8	14	0	17"L x 11"W x 16"H	7.0 lbs.
CTB2010	20" Contractor Bulk Bag	11	19	26	20"L x 12.2"W x 13"H	4.8 lbs.
CTB1000	Backpack	4	34 internal front pockets	0	14"L x 10"W x 18"H	8.0 lbs.

Crescent JOBBOX Mesh Cabinet Storage

New Crescent JOBBOX Mesh Cabinets keep tools and supplies visible for maximum productivity with the security of 13 gauge steel mesh walls and a commercial duty 3-point door lock system that secures doors at the top, bottom and center. High-visibility white shelves offer multiple positions for maximum storage capacity and versatility, while built-in door bins and an external mounted shelf for tall items add utility.



COMMERCIAL



3-POINT
LOCK

RUGGED

13 GAUGE
STEEL MESH

HEAVY DUTY



6" CASTERS



1-401990

Door Hasps
For padlock



1-402990

Continuous Door Hinges
Provide long-term
durability

Part No.	Description	Length	Width	Height	Weight	Shelves	Casters	Load Capacity
1-400990	65" Mesh Cabinet	75 in	33 in	55 in	375 lbs.	5	2 Fixed & 2 Locking/Swivel	Total 1,500 lbs; Shelf 200 lbs.
1-401990	49.5" Mesh Cabinet	59.5 in	33 in	55 in	328 lbs.	5	2 Fixed & 2 Locking/Swivel	Total 1,400 lbs; Shelf 200 lbs.
1-402990	33" Mesh Cabinet	42.5 in	33 in	51.25 in	215 lbs.	3	2 Fixed & 2 Locking/Swivel	Total 1,000 lbs; Shelf 200 lbs.

Crescent JOBBOX Manual-Closing Safety Cabinets

Keep flammable liquids organized, secure, and protected from fire with UL listed Crescent JOBBOX Safety Cabinets. With exclusive features like EZ Level™ bolsters (excludes 12 gallon), permanent safety labels, and white shelves, these cabinets offer improved safety with the security and durability Crescent JOBBOX storage products are known for.

5 YR.
LIMITED
WARRANTY

CLICK HERE

18 Gauge Double Wall and Superior Construction
Far surpassed UL Testing requirements

High/Low Vent Connections

Tilted Spill-Guide Interior Shelving
Directs spills to the back of the cabinet and into the retention sump area for easy clean up

Staked and Welded Hinges
14-gauge steel, 3/8" continuous hinge with extra-large 1" knuckles provides the ultimate in protection. It's 1/4" steel pin can't be driven or pried out

Extra Heavy Duty 1 3/4" Thick Doors
Provide greater insulation between door panels

Powder Paint Finish
Superior resistance to abrasion, weather, UV and scratch damage

EZ-Level™ Skid Bolsters
Constructed with a leveling screw access hole, providing easy access when leveling the cabinet is necessary. The anti-tip design provides maximum stability and tipping resistance. (excludes 12 Gal.)



SPILL GUIDE

SHELVING

BRIGHT WHITE

INTERIOR

HI-VIZ

SAFETY LABELS

Burn Test Results

To receive UL certification, a cabinet must pass a 10 minute burn test. The UL burn test heats the outside of the cabinet to +1,250°F for 10 minutes and the interior of the cabinet must remain below 325°F to pass. A leading competitor failed the UL certificate because its interior was +700°F. Crescent JOBBOX passed the UL certificate with interior temperatures below 250°F.***

700°F

250°F

Yellow Safety Cabinet

Red Safety Cabinet

Green Safety Cabinet

UL LISTED

Yellow Safety Cabinets are industry standard yellow for storage of flammable liquids.

Part No.	Capacity	Exterior Dimensions H x W x D	Interior Dimensions H x W x D	Doors	Shelves	Compliance / Listings	Shipping Wt.
1-750640	12 gallon	37-3/16" x 30-13/32" x 23-19/32"	26-31/32" x 26-27/32" x 16"	1	1	UL, NFPA, OSHA	175 lbs.
1-753640	30 gallon	45-23/32" x 46-5/16" x 20- 25/32"	32-1/16" x 42-5/8" x 16-23/32"	2	1	UL, NFPA, OSHA	276 lbs.
1-756640	45 gallon	66-23/32" x 46-5/16" x 24"	53-1/32" x 42-5/8" x 16-23/32"	2	2	UL, NFPA, OSHA	363 lbs.
1-758640	60 gallon	66-23/32" x 46-5/16" x 27-7/8"	53-1/32" x 42-5/8" x 23-13/16"	2	2	UL, NFPA, OSHA	421 lbs.
1-759640	90 gallon	66-23/32" x 46-5/16" x 34-1/16"	53-1/32" x 42-5/8" x 26-25/32"	2	2	UL, NFPA, OSHA	465 lbs.

Red Safety Cabinets are industry standard red for storage of paints, inks, and other combustibles.

Part No.	Capacity	Exterior Dimensions H x W x D	Interior Dimensions H x W x D	Doors	Shelves	Compliance / Listings	Shipping Wt.
1-750610	12 gallon	37-3/16" x 30-13/32" x 23-19/32"	26-31/32" x 26-27/32" x 16"	1	1	UL, NFPA, OSHA	175 lbs.
1-753610	30 gallon	45-23/32" x 46-5/16" x 20- 25/32"	32-1/16" x 42-5/8" x 16-23/32"	2	1	UL, NFPA, OSHA	276 lbs.
1-756610	45 gallon	66-23/32" x 46-5/16" x 24"	53-1/32" x 42-5/8" x 16-23/32"	2	2	UL, NFPA, OSHA	363 lbs.
1-758610	60 gallon	66-23/32" x 46-5/16" x 27-7/8"	53-1/32" x 42-5/8" x 23-13/16"	2	2	UL, NFPA, OSHA	421 lbs.
1-759610	90 gallon	66-23/32" x 46-5/16" x 34-1/16"	53-1/32" x 42-5/8" x 26-25/32"	2	2	UL, NFPA, OSHA	465 lbs.

Green Safety Cabinets are industry standard green for storage of outdoor chemicals.

Part No.	Capacity	Exterior Dimensions H x W x D	Interior Dimensions H x W x D	Doors	Shelves	Compliance / Listings	Shipping Wt.
1-750620	12 gallon	37-3/16" x 30-13/32" x 23-19/32"	26-31/32" x 26-27/32" x 16"	1	1	UL, NFPA, OSHA	175 lbs.
1-753620	30 gallon	45-23/32" x 46-5/16" x 20- 25/32"	32-1/16" x 42-5/8" x 16-23/32"	2	1	UL, NFPA, OSHA	276 lbs.
1-756620	45 gallon	66-23/32" x 46-5/16" x 24"	53-1/32" x 42-5/8" x 16-23/32"	2	2	UL, NFPA, OSHA	363 lbs.
1-758620	60 gallon	66-23/32" x 46-5/16" x 27-7/8"	53-1/32" x 42-5/8" x 23-13/16"	2	2	UL, NFPA, OSHA	421 lbs.
1-759620	90 gallon	66-23/32" x 46-5/16" x 34-1/16"	53-1/32" x 42-5/8" x 26-25/32"	2	2	UL, NFPA, OSHA	465 lbs.

Crescent JOBBOX Self-Closing Safety Cabinets

With Crescent JOBBOX Self-Closing Cabinets, users can work freely with peace of mind knowing that their flammable liquids will be secure. Extra-robust fusible link system will operate at 165°F to close the doors, and a heavy-duty, galvanized staggering mechanism ensures the doors close securely in the event of a fire. Fully enclosed, the Crescent JOBBOX self-closing system ensures safe operation while offering maximum storage space inside the cabinet.



Self-Latching 3-Point Door Locking System

Includes a heavy-duty enclosed staggering mechanism that ensures the doors close in proper order. The fusible link assembly disconnects at 165° F to close doors and keep danger inside.

Highly Visible Safety and Warning Labels

A permanent reminder and reference for following proper safety and usage practices

Secure 3-Point Lock System

Featuring a rugged lockable paddle handle that restricts access and reduces theft potential

Bright Interior

Aids in identifying when spills have occurred

Extra Heavy Duty 1 3/4" Thick Doors

Provide greater insulation between door panels

Powder Paint Finish

Superior resistance to abrasion, weather, UV and scratch damage

EZ-Level™ Skid Bolsters

Constructed with a leveling screw access hole, providing easy access when leveling the cabinet is necessary. The anti-tip design provides maximum stability and tipping resistance. [excludes 12 Gal.]



EZ-LEVEL™



SKID BOLSTERS

SPILLGUIDE



SHELVING


SELF-CLOSING



DOOR LOCK

Burn Test Results

To receive UL certification, a cabinet must pass a 10 minute burn test. The UL burn test heats the outside of the cabinet to +1,250°F for 10 minutes and the interior of the cabinet must remain below 325°F to pass. A leading competitor failed the UL certificate because its interior was +700°F. Crescent JOBBOX passed the UL certificate with interior temperatures below 250°F.***



Yellow Safety Cabinets are industry standard yellow for storage of flammable liquids.

Part No.	Capacity	Exterior Dimensions H x W x D	Interior Dimensions H x W x D	Doors	Shelves	Compliance / Listings	Shipping Wt.
1-754640	30 gallon	45-23/32" x 46-5/16" x 20- 25/32"	32-1/16" x 42-5/8" x 16-23/32"	2	1	UL, NFPA, OSHA	285 lbs.
1-757640	45 gallon	66-23/32" x 46-5/16" x 24"	53-1/32" x 42-5/8" x 16-23/32"	2	2	UL, NFPA, OSHA	372 lbs.

Red Safety Cabinets are industry standard red for storage of paints, inks, and other combustibles.

Part No.	Capacity	Exterior Dimensions H x W x D	Interior Dimensions H x W x D	Doors	Shelves	Compliance / Listings	Shipping Wt.
1-754610	30 gallon	45-23/32" x 46-5/16" x 20- 25/32"	32-1/16" x 42-5/8" x 16-23/32"	2	1	UL, NFPA, OSHA	285 lbs.
1-757610	45 gallon	66-23/32" x 46-5/16" x 24"	53-1/32" x 42-5/8" x 16-23/32"	2	2	UL, NFPA, OSHA	372 lbs.

Green Safety Cabinets are industry standard green for storage of outdoor chemicals.

Part No.	Capacity	Exterior Dimensions H x W x D	Interior Dimensions H x W x D	Doors	Shelves	Compliance / Listings	Shipping Wt.
1-754620	30 gallon	45-23/32" x 46-5/16" x 20- 25/32"	32-1/16" x 42-5/8" x 16-23/32"	2	1	UL, NFPA, OSHA	285 lbs.
1-757620	45 gallon	66-23/32" x 46-5/16" x 24"	53-1/32" x 42-5/8" x 16-23/32"	2	2	UL, NFPA, OSHA	372 lbs.

Crescent JOBBOX Mobile Field Office

Making your work easier and better organized, your new 33" deep Crescent JOBBOX Mobile Field Office rolls through 36" commercial doorways and is designed for you to easily add digital connectivity with a monitor, backup battery power and printer. Its reinforced construction, built-in lockable security, and heavy duty 6" locking casters ensure years of service, security, and convenience.



Removable Shelf
For easy digital office conversion

Door Safety Pin Latch
Prevents accidental door closing

Rain Gutters
Divert water away from doors

Steel Pegboard
For hanging storage of smaller items

Sidewall Storage
Provides organization of smaller items

3 Position Lockable Desktop
Can be propped into a flat working surface

Slide Out Shelf
Designed to accommodate a printer and other large items

Patented One Handle Lock Operation
Opens top and bottom doors

Built-In Door Storage Shelves
Provides additional storage



SKY-JACK



FORK
RETAINERS

HOIST



RINGS

WEATHER



STRIPPING

LID LOWERING



ASSIST
SHOCK

6" LOCKING



CASTERS



1,500 lbs.
Capacity
Lifting Hooks

Heavy Duty
6" Casters
Included



Designed for Digital Conversion

Our new Mobile Field Office features a removable upper shelf that provides room to add up to two monitors. The unit also features an external power entry point, multiple pass-through locations for wiring, and built-in shelf positions for chargers.

Designed for High Mobility

Our new Mobile Field Office is sized to roll through 36" commercial doorways on Heavy Duty 6" Locking Casters. Sky-Jack Fork Retainers provide safe lifting and four corner-mounted Hoist Rings are rated for a 1500 lb. working load capacity.

Part No.	Description	Length	Material	Shipping Weight	Shipping Cubic Feet
1-510990	Mobile Field Office	63 in	Steel	581 lbs.	83.6³

Crescent JOBBOX Onsite Chests

Designed for security, easy access and excellent weather resistance, the Crescent JOBBOX Chest yields an abundance of features including four-way skid bolsters, and a visual, three-point locking system.

* COMING SOON! Available early 2020

Reinforced Lid with Full Length Bolster

Reduces damage from excess stacking weight and resists pry bar entry

Site-Vault® Security System

The patented system has a full-length steel lock console with three locking points and fluorescent reflective orange tape that indicates chest is locked

Commercial Gas Springs

Helps raise and safely lower lid

Dual Built-In Lid Storage Bins

Cargo nets hold items like first aid kit, rain gear, manuals, safety items

EZ-Lock Arm

Securely locks lid open

Built-In Bin Storage

Quick access for small tools and parts

Recessed Handles

Prevent pinched fingers and damage to the handle

Heavy Gauge Steel Skid Bolsters

Provide easy load or unload from any side



Chamfered Lid Edge

Improves safety by eliminating sharp corners and enhances security with stronger lid reinforcement

Site-Vault® Security System

Reinforces lid front against pry bar entry

Upgraded Lock System

Uses Master # 1, # 5, #175 and American 50

Channel and Formed Lower Panel

Adds strength and resists denting

2-654990

Part No.	Description	Length	Width	Height	Shipping Cubic Feet	Shipping Weight
2-651990	30" Portable Security Chest	30 in	20 in	19.75 in	6.9 ft³	60 lbs.
2-652990	36" Chest	36 in	20 in	27.5 in	11.5 ft³	98 lbs.
2-653990	42" Chest	42 in	20 in	27.5 in	13.4 ft³	118 lbs.
2-654990	48" Chest	48 in	24 in	30.75 in	20.5 ft³	148 lbs.
2-655990	60" Chest	60 in	24 in	30.75 in	25.6 ft³	182 lbs.
2-656990	48"x 30" Chest	48 in	30 in	36.75 in	30.6 ft³	190 lbs.
2-657990	60" Drop Front Chest	60 in	31 in	45 in	48.4 ft³	320 lbs.
2-658990	72" Chest	72 in	24 in	30.75 in	30.8 ft³	203 lbs.

Crescent JOBBOX Piano Boxes

The perfect combination of storage space, organization, and security, the world renowned Crescent JOBBOX Piano Box is a job site must-have. Two storage bins on both side walls and the Crescent JOBBOX Lift-n-Stow Shelf give you room to store any item, while the Site-Vault™ lock system ensures that your valuables remain safe and secure.

* COMING SOON! Available early 2020



SITE-VAULT™



SECURITY
SYSTEM

GAS SPRING



GUARDS

OPTIONAL



CASTERS

Heavy Gauge Steel Skid Bolsters

Provide easy load or unload from any side



Formed Side Wall Design

Allows door to overlap walls when closed — providing rigid security and protection from wind driven rain

Recessed Handles

Prevent pinched fingers and damage to the handle

Part No.	Description	Length	Width	Height	Shipping Cubic Feet	Shipping Weight
2-681990-01	48" Piano Box	48 in	31 in	51 in	43.9 ft³	297.7 lbs.
2-682990-01	60" Piano Box	60 in	31 in	51 in	54.9 ft³	353.7 lbs.
2-688990-01	60" Short Height Piano Box	60 in	31 in	39 in	42 ft³	279.1 lbs.
2-689990-01	72" Piano Box	74 in	31 in	51 in	67.7 ft³	413.2 lbs.
2-683990-01	60" Drop Front Piano Box	60 in	31 in	51 in	54.9 ft³	380 lbs.
2-684990-01	74" Drop Front Piano Box	74 in	31 in	51 in	67.7 ft³	437 lbs.
2-685990-01	74" High Capacity Piano Box	74 in	35 in	64 in	80.9 ft³	519.5 lbs.

Crescent JOBOX 60" Two-Door Cabinet

Organization how you want it. With four models to choose from with varying storage capacity and door options, JOBOX Cabinets give you the power to make organizing your job site, plant floor, or maintenance bay a cinch. With the innovative foot operated latch and anti-tip bolsters, you also get first class accessibility and safety features.

Nearly 17 Linear Ft.
of Door Storage

Fully-Welded
Padlock Housing

Three 5/8" Steel
Locking Pins Per
Door

Welded Corner
Gussets
Reinforce body



High-Strength
Heavy-Duty Shelves

Hand or Foot
Operated Door Latch

Access Holes for
Electrical Cables

Three Heavy Duty
Lock Hooks Per Door




EZ-LOADER™



SKID
BOLSTERS

RECESSED



HANDLES

OPTIONAL



CASTERS

CRESCENT
JOBBOX®



LISTED



Because in a Crisis, Every
Second Counts

UL-tested Crescent JOBOX Safety Cabinets keep flammable and hazardous liquids organized, secure, and protected from fire. With exclusive features like EZ Level™ bolsters, permanent safety labels, and white interiors, these cabinets offer improved safety with the security and durability Crescent JOBOX storage products are known for.

© 2018 Apex Tool Group, LLC



Trusted by the Trades.

See the entire line of Crescent
brand products now at
www.crescenttool.com.

Part No.	Description	Length	Width	Height	Shipping Weight	Cubic Feet
1-694990	60" Two-Door Cabinet	60.75 in	24.25 in	60.25 in	379 lbs.	53.2

Crescent Lufkin Shockforce® and Shockforce Nite Eye® Measuring Tapes

Introducing the toughest tapes to ever hit a jobsite. Shockforce brings new meaning to the term high performance with a full 14 feet of standout* and the ability to survive a 100-foot drop. Add in a diamond coated 360-degree end hook that delivers 50% more gripping power, a two-sided blade with vertical markings on the back, and class-leading ergonomics and you have a tape that’s destined to be the new standard for trade professionals.

But that’s not all. There’s also the Shockforce Nite Eye, with all the capabilities of the original Shockforce plus the Nite Eye high visibility green-on-matte black blade. Made for superior legibility in any light condition — from bright sun to dim interiors — Shockforce Nite Eye helps you measure even faster.

Superior Impact Protection

Dual metal guardrails on both sides of the lock button provide superior protection

Integrated Thru-Hole

Can be used as a tether loop attachment point when working at height or as a pivot for scribing arcs

High Visibility No-Glare Blade

High-contrast green markings and matte finish provide improved legibility in all light conditions

Durable Nylon Blade Coating

Best-in-class blade protection, extending blade life 5X vs. standard uncoated blades

360-Degree End Hook

Diamond abrasive-coated, our end hook grips surfaces better to save time when measuring

*at maximum performance



Time Saving Two-Sided Blades

Blades on both Shockforce and Shockforce Nite Eye are two-sided with vertical markings on the back for quicker and easier measuring

- NYLON
- 5X BLADE LIFE COATING
- 2-SIDED BLADES
- TETHER READY



Item No	Description	Blade	Blade Dimensions	Inner Pack Qty.	Master Pack Qty.
L1116	16' Shockforce Tape Measure	Yellow Nylon Coated	16' x 1-3/16"	4	16
L1125	25' Shockforce Tape Measure	Yellow Nylon Coated	25' x 1-3/16"	4	16
L1135	35' Shockforce Tape Measure	Yellow Nylon Coated	35' x 1-3/16"	4	16
L1116B	16' Nite Eye Tape Measure	Black Nylon Coated	16' x 1-3/16"	4	16
L1125B	25' Nite Eye Tape Measure	Black Nylon Coated	25' x 1-3/16"	4	16
L1135B	35' Nite Eye Tape Measure	Black Nylon Coated	35' x 1-3/16"	4	16
L1116	5M /16' Shockforce Tape Measure	Yellow Nylon Coated	5M /16' x 1-3/16"	4	16
L1125CME	8M /26' Shockforce Tape Measure	Yellow Nylon Coated	8M /26' x 1-3/16"	4	16
L1135CME	10M /33' Shockforce Tape Measure	Yellow Nylon Coated	10M /33' x 1-3/16"	4	16

Easier Inside Measurements

25-foot tapes have an even 3-inch adder, making inside measurement calculations fast and easy

Crescent Lufkin Control Series Tape Measures

The Crescent Lufkin Control Series is right at home in the hands of professionals. The 1-3/16” wide tape with extra-large print has 12 feet of stand-out* to tackle any job, and the matte finish both reduces glare and protects the blade, ensuring that it holds up through heavy use. The finger brake allows the user to control the blade without risk of pinching, and the blade can be locked in place with the wide lock button protected by over-mold rails. The best-in-class durability of the Control Series doesn’t stop at the lock button rails — the ergonomic case survived 50+ 1-story drops in real life strength testing.

Ergonomic Case
Touch point texture for increased grip and more comfortable handling

Lock Button Rails
Over-mold rails protect the lock button during drops for improved durability

Protective Blade Coating
Matte finish for reduced glare and extended blade life

360-Degree End Hook
Grips from all sides for more efficient measuring

Finger Brake
Safely control blade retraction without pinching fingers

Tether Point
Integrated slot for tethering tape when working at height

FINGER TIP

CONTROL

DURABLE
3x LIFE

COATING

VERSATILE
360°

END HOOK

Item No	Description	Blade	Blade Dimensions	Inner Pack Qty.	Master Pack Qty.
L1016C	16' Control Series Tape Measure	Yellow Nylon Coated	16'X1-3/16"	6	24
L1025C	25' Control Series Tape Measure	Yellow Nylon Coated	25'X1-3/16"	6	24
L1025CB	25' Control Series Tape Measure	Black Nylon Coated	25'X1-3/16"	6	24
L1025CD	25' Control Series Tape Measure, Engineers	Yellow Nylon Coated	25'X1-3/16"	6	24
L1025CME	8M/26' Control Series Tape Measure	Yellow Nylon Coated	8M/26'X1-3/16"	6	24
L1030C	30' Control Series Tape Measure	Yellow Nylon Coated	30'X1-3/16"	6	24
L1035C	35' Control Series Tape Measure	Yellow Nylon Coated	35'X1-3/16"	6	24
L1035CME	10M/33' Control Series Tape Measure	Yellow Nylon Coated	10M/33'X1-3/16"	6	24

*at maximum performance



- Textured case for easier grip and increased comfort
- Matte blade finish reduces glare and increases legibility
- Serrated end hook allows users to mark measurements without a writing utensil
- Compact size fits nicely into a tape holder or pocket

Crescent Lufkin 600 Series HI-VIZ Power Tapes

Item No	Description	Blade	Blade Dimensions	Inner Pack Qty.	Master Pack Qty.
L610N	10' Power Tape, 1/2" Hi Viz Orange	Yellow Clear Coated	10' x 1/2"	6	36
L610CMEN	3M/10' Power Tape, 1/2" (13mm) Hi Viz Orange	Yellow Clear Coated	3M/10' x 1/2"	6	36
L616N	16' Power Tape, 3/4" Hi Viz Orange	Yellow Clear Coated	16' x 3/4"	6	36
L616CMEN	5M/16' Power Tape, 3/4" (19mm) Hi Viz Orange	Yellow Clear Coated	5M/16' x 3/4"	6	36
L625N	25' Power Tape, 1" Hi Viz Orange	Yellow Clear Coated	25' x 1"	8	16
L625CMEN	8M/26' Power Tape, 1" (25mm) Hi Viz Orange	Yellow Clear Coated	8m/26' x 1"	8	16



- Wide 1" blade delivers 8ft of stand-out
- Durable, mirror-finish chrome case
- Quad-riveted end hook for long life
- Extra-wide lock button for easy thumb actuation
- Matte finish, nylon coated blade for glare reduction and extra blade protection

Crescent Lufkin 900 Series Classic Power Tapes

Item No	Description	Blade	Blade Dimensions	Inner Pack Qty.	Master Pack Qty.
L912	12' Legacy Power Tape, 3/4"	Yellow Nylon Coated	12' x 3/4"	6	36
L916L	16' Legacy Power Tape, 1"	Yellow Nylon Coated	16' x 1"	6	36
L925L	25' Legacy Power Tape, 1"	Yellow Nylon Coated	25' x 1"	6	24
L930L	30' Legacy Power Tape, 1"	Yellow Nylon Coated	30' x 1"	6	24
L935L	35' Legacy Power Tape, 1"	Yellow Nylon Coated	35' x 1"	6	24
L912CME	3.7M/12' Legacy Power Tape, 19mm	Yellow Nylon Coated	3.7M/12' x 3/4"	6	36
L916CME	5M/16' Legacy Power Tape, 25mm	Yellow Nylon Coated	5M/16' x 1"	8	16
L925CME	8M/26' Legacy Power Tape, 25mm	Yellow Nylon Coated	8M/26' x 1"	8	16
L933CME	10M/33' Legacy Power Tape, 25mm	Yellow Nylon Coated	10M/33' x 1"	6	18

Crescent Lufkin Construction Long Tapes

The Crescent Lufkin Construction Long Tapes are ideal for measuring long distances around your home or on the job. Available in multiple lengths and blade styles, the long tapes are designed to be durable and long lasting, regardless of the application they're used for.

BLADE

GUARD

FASTER
3x REWIND

STRONGER
42_{CT}

BLADE



Dual-Material Grip
Elevated above the reel prevents contact between reel and knuckles

Tuck Away Handle
Prevents handle from snagging and breaking during transportation and storage

Versatile Folding End Hook
Hook opens for improved grasp during use and collapses during storage

Dual Material Case
Rubber over-mold grip areas for increased durability, added comfort and control

3:1 Gear Ratio for Fast Rewinding
Helps get jobs done faster

Dual-Sided Printed Blade
SAE markings on top and metric on bottom; nylon coating provides longer blade life

Item No	Description	Blade Width	Blade Material	Inner Pack Qty	Case Pack Qty
ST100	100' Steel SAE/Metric Dual Sided Tape Measure	3/8"	Steel	5	20
FE100N	100' Fiberglass SAE/Metric Dual Sided Tape Measure	1/2"	Fiberglass	-	6
FE300N	300' Fiberglass SAE/Metric Dual Sided Tape Measure	1/2"	Fiberglass	-	2

Crescent Lufkin Measuring Wheels

The Crescent Lufkin Centerline Balance Measuring Wheels are designed for ultimate accuracy. The single, center mounted wheel provides superior balance and maneuverability. The wheel's counter has a gear drive, which is more durable and delivers greater long-term accuracy than belt-drive counters. The counter readout is positioned above the wheel, closer to the user for maximum visibility and ease of use.

GEAR

DRIVE

ANTI-BREAK

DRIVE

CENTERLINE

BALANCE

WHEEL

WIPER



Heavy-Duty Counter Reset

Counter Readout
Positioned above wheel for improved readability

Centered Single Wheel
For improved balance and maneuverability

Folding Handle
Sturdy damage-resistant breakaway joint

Wheel Wiper
Prevents mud build-up for consistent results

Centered Single Wheel
For improved balance and maneuverability

Heavy-Duty, Gear Drive Counter
For superior accuracy and durability vs. belt drive designs

Telescoping Handle
For infinite fit adjustment

CLICK HERE

Item No	Description	Extended Length	Folded Length	Order Pack Qty
PSMW48CL	12" Professional Measuring Wheel	38.5"	20"	2
PSMW18N	4" Compact Measuring Wheel	45.0"	25.5"	6

Crescent Wiss Next Generation Aviation Snips

Continuous improvement means never being satisfied. That’s why these new Next Generation snips last 60% longer and require 20% less force to cut on average compared to our snips from just five years ago. And that’s why Crescent Wiss is the undisputed leading brand of snips for sheet metal professionals.

Ergonomic Non-Slip Grips
Provide excellent control and easy cleaning

Ergonomic Latch
For fast, single-handed operation with either hand

Integrated Handle Ring
For hanging or easy storage

Improved Pivot Design
Features built-in stops for consistent jaw opening and upgraded spring action for fast, effortless feed

Superior Blade Serrations
Our proprietary process creates finer serrations and spreads the force of the cut across the blades for a better material grip and longer blade life

Precision Cast Blades
Our blades have amazing strength, precision, and consistency due to our exclusive casting method



CUTS 8
MILES
OF STEEL*

UP TO
10X
CUT LIFE



M1R



M2R



M3R



M5R



M6R



M7R



M8OS

Item No	Description	Handle Color	Product Package Dimensions	Product Weight
M1R	Aviation Snip, Left Cut	Red	11.5”L x 3.3”W x 1”H	.40 lbs.
M2R	Aviation Snip, Right Cut	Green	11.5”L x 3.3”W x 1”H	.40 lbs.
M3R	Aviation Snip, Straight Cut	Yellow	11.5”L x 3.3”W x 1”H	.40 lbs.
M5R	Bulldog Snip	Red	11.5”L x 3.3”W x 1”H	.40 lbs.
M6R	Aviation Snip, Offset Left Cut	Red	11.5”L x 3.3”W x 1”H	.40 lbs.
M7R	Aviation Snip, Offset Right Cut	Green	11.5”L x 3.3”W x 1”H	.40 lbs.
M8OS	Aviation Snip, Offset Straight Cut	Yellow	11.5”L x 3.3”W x 1”H	.40 lbs.



M45RS

- Perfect for cutting all types of small molding in PVC, MDF, and pine
- Fast miter cuts with no power —so no mess
- Built-in angle finder with marks for 120, 105, 90, 75, and 60 degrees with a built-in stop at 45
- Blade is able to be sharpened for prolonged use
- Non-slip grips for easy cleaning and better control
- Durable steel construction

Crescent Wiss Molding Miter Snip

Item No	Description	Handle Color	Product Package Dimensions	Product Weight
M45RS	Molding Miter Snip	Rawhide Orange	11.0"L x 4.8"W x 1.75"H	.40 lbs.



WKAR2

- Blade retracts automatically the moment it loses contact with the material being cut
- Helps reduce workplace injuries
- Accepts all standard utility knife blades
- Quick and easy blade change
- Blade storage compartment in the handle holds additional blades

Crescent Wiss Knives

Item No	Description	No. of Blades Included	Product Packaging Dimensions	Weight
WKF2	Folding Utility Knife	11	9.6"L x 3.5"W x 1.7"H	0.60 lbs.
WKAR2	Auto Retract Safety Knife	3	8.9"L x 4.9"W x 1.6"H	0.50 lbs.

Crescent Wiss HVAC Tools



WF12

- Constructed of heavy 16 gauge steel
- Keeps folding channels from widening and ensures accurate bends

Folding Tools

Item No	Description	Folding Channel Depth	Product Weight
WF12	12" Folding Tool	3/8" and 1"	1.30 lbs.
WF18	18" Folding Tool	3/8" and 1"	2.00 lbs.
WF24	24" Folding Tool	3/8" and 1"	2.70 lbs.



WS3N

- Optimal handle span for maximum power from an ergonomic operating range
- Non-slip cushion grips for superior comfort and control
- Produces a permanent, tight-fitting seam

Seamers

Item No	Description	Jaw Width	Product Length	Product Weight
WS3N	3" Hand Seamer	3-1/4 in	9-1/4 in	1.35 lbs.
WS4N	3" Offset Hand Seamer	3-1/4 in	9 in	1.40 lbs.
WS6N	6" Hand Seamer	6 in	9-1/4 in	1.90 lbs.



WC5SN

- Crimps up to 22 gauge galvanized steel pipes
- Optimal handle span provides maximum power from a comfortable operating range
- Non-slip cushion grips for comfort and control
- Tanto-style serrated blade
- Compound action jaw provides excellent comfort and control

Crimpers

Item No	Description	Throat Depth	Product Length	Product Weight
WC3SN	3-Blade Crimper	1-1/4 in	9-3/4 in	0.85 lbs.
WC5SN	5-Blade Crimper	1-1/4 in	9-3/4 in	0.95 lbs.



WT1

- Easy to operate cut off mechanism that trims excess cable strap
- Comfortable cushion grip handles and internal stop

Cable Tie Tensioning Tool

Item No	Description	Cable Tie Width	Product Length	Product Weight
WT1	Cable Tie Tensioning Tool	up to 3/8"	7-1/2 in	0.90 lbs.

New and Improved Crescent Wiss Tradesman Shears

From our compact Electrician/Data Scissor to our Heavy-Duty Spring Loaded Tradesman Shear, this line of shears and scissors offers the features, strength, and durability professional users need. Every one is purpose-built to deliver outstanding comfort, superior results, and long life. High-performance models feature titanium-coated blades for smooth, powerful cuts and several have a full metal core for maximum strength and durability.

COMING SOON! Available early 2020



Ergonomic Design
Optimizes handle contact points to maximize comfort and control

Full Metal Core
Extends through handle for durability and strength

Heavy Duty Titanium Coated Blades
For powerful cutting

Serrated Bottom Blade
Grips material for greater control

Control Channel
Accommodates index finger for increased control

Item No	Description	Tool Length	Blade Length	Handedness
CW5T	Electrician/Data Scissor	6-1/2 in	1-3/4 in	Ambidextrous
CW7T	Heavy-Duty Utility Shear	7-1/2 in	2 in	Ambidextrous
CW812S	All-Purpose Scissor	8-1/2 in	3-1/4 in	Ambidextrous
CW10T	Offset Professional Shear	9-1/2 in	3-3/4 in	Right Handed
CW10TL	Left-Handed Offset Professional Shear	9-1/2 in	3-3/4 in	Left Handed
CW10TM	Heavy-Duty Tradesmen Shear	10 in	4 in	Right Handed
CW11TM	Heavy-Duty Spring Loaded Tradesmen Shear	10-1/2 in	4 in	Ambidextrous



Crescent H.K. Porter Double Compound Action Bolt Cutter with PowerPivot™

An industrial-grade bolt cutter featuring more cutting power with 30% less effort. It's the perfect solution for production facilities, maintenance and repair operations, utilities, construction sites, oil and gas operations and more. The unique PowerPivot™ geometry was developed using advanced computer-aided design to create a double compound action system with greater efficiency than competitive bolt cutters. Together with specially engineered HKP blades, PowerPivot™ bolt cutters deliver superior strength with a 30% reduction in effort to cut when cutting.

Exceptional Capacity
Cuts harder and larger diameter materials up to 5/16" HRC-48 materials for 24" model and 9/32" HRC-48 for the 18" model

Ultimate Blade Durability
Precision ground, induction hardened cutting blades for extended edge life and cutting hard materials

30% LESS EFFORT
POWER PIVOT.
MORE POWER

High-Performance Handles
Tubular steel handles for extra strength and cutting power

THE POWER PIVOT™ ADVANTAGE >>>
Double Compound Action PowerPivot™ provides more power and a 30% less effort for easier cutting.

CLICK HERE

0090MCP


Item No	Description	Max Cut Capacities:		
		Soft Materials [HRC-31]	Medium Materials [HRC-42]	Hard Materials [HRC-48]
0090MCP	18" PowerPivot™ Bolt Cutter	3/8"	5/16"	9/32"
0190MCP	24" PowerPivot™ Bolt Cutter	7/16"	3/8"	5/16"



- Drop-forged precision ground, alloy tool steel jaws with center-cut blades
- Lockplate keeps jaws from loosening
- Toggle joints turn 50 lbs. hand pressure to 4000 lbs. of cutting pressure
- Joint multiplies the handle pressure into 80x the cutting power
- Proudly made in the USA

Crescent H.K.Porter Bolt Cutters

Item No	Description	Max Cut Capacities:		Product Weight
		Soft Materials [HRC-31]	Hard Materials [HRC-48]	
0090MC	18" Bolt Cutter	3/8"	1/4"	3.70 lbs.
0190MC	24" Bolt Cutter	7/16"	5/16"	6.45 lbs.



- 14-position indexing head adjusts with push button to allow total access for maximum leverage
- Extra-sturdy steel handles
- Super-strong indexing head grips securely for accurate bends

Crescent H.K.Porter Rebar Benders

Item No	Description	Product Length	Max Capacity	Product Weight
RB4	3/8 in, 1/2 in, #3 and #4 Extending Rebar Bender	22-3/4 in, 35 in	3/8", 1/2"	4.70 lbs.
RB5	5/8 in, #5 Rebar Bender	44-1/4 in	5/8"	8.75 lbs.
RB6	3/4 in, #6 Rebar Bender	44-1/4 in	3/4"	8.75 lbs.
0590RBJN	Rebar Cutter Bender	52 in	5/8"	44.00 lbs.



- Sheer-cut blades
- Excellent for cutting pallet straps when loading and unloading freight cars, trucks or ships
- Long-handled, goose neck, 2-hand operated cutter
- Proudly made in the USA

Crescent H.K.Porter Strap Cutters

Item No	Description	Length	Flat Steel Strap	Product Weight
0990T	3/4" Capacity Steel Strap Cutter	9 in	3/4 in x .035 in, 19mm x 1 mm	1.25 lbs.
1290G	1-1/4" Capacity Strap Cutter	13.5 in	1-1/4 in x .050 in, 32mm x 1 mm	1.70 lbs.
2690GP	Heavy Duty Steel Strap Cutter	25-1/4 in	2 in x .050 in, 51mm x 1 mm	6.80 lbs.



- Notched shear-cut blades hold material firmly in place
- Ratchet and chain design produces easy, progressive cuts
- Makes clean, square cuts with minimal distortion

Crescent H.K.Porter Ratcheting Guy Strand Cutter

Item No	Description	Length	EHS Guy Strand	Common Guy Strand	Product Weight
8690CK	Guy Strand Ratchet Cutter	28 in	1/2 in, 13 mm	1/2 in, 13 mm	10.34 lbs.



- Jaw keeper prevents jaws from spreading while under heavy load
- Shear-cut blades
- Ratchet and chain design increase cutting pressure as handles open and close
- Can be used effectively with short strokes in confined spaces

Crescent H.K.Porter Ratcheting Hard Cable Cutter

Item No	Description	Length	ACSR, ACAR, ZEBRA and Telephone Cable [Self Supporting]	Product Weight
8690FH	Hard Cable Ratchet Cutter	29-1/4 in	1-3/16 in, 30 mm	12.4 lbs.



- Jaw keeper prevents jaws from spreading while under heavy load
- Heavy-duty jaw design
- Ratchet provides up to 5x the mechanical advantage over manual cutters

Crescent H.K.Porter Ratcheting Soft Cable Cutter

Item No	Description	Length	Copper and Aluminum Cable, Power/Comm Cable	Product Weight
8690FSK	Soft Cable Ratchet Cutter	29-3/4 in	3 in, 73 mm	12.6 lbs.



- Ratchet-type jaws with notched shear-cut blades
- Blades hold and lock material in place during the cut
- Cuts all strands with minimal crushing or distortion

Crescent H.K.Porter Ratcheting Wire Rope Cutter

Item No	Description	Length	EHS Guy Strand	Aircraft Cable, Hard Stainless Steel Cable	Product Weight
8690TN	Wire Rope Ratchet Cutter	36 in	5/8 in, 16 mm	5/8 in, 16 mm	11.0 lbs.



Everyday Carry.
These new bags are built to last.

You demand a lot from your tools. It's time to demand the same from your tool bag. Every Crescent bag is built to last with a hard polypropylene base and genuine YKK zippers guaranteed for 3 full years. Check out the new line of tradesman bags from Crescent. Made for strength. Made to last. Made for the long haul.

Trusted by the Trades.



See the full lineup:
www.crescenttool.com



Crescent Nicholson General Purpose Dual-Sided
File with Bastard and Smooth Cuts

These American pattern flat files have a bastard cut on one side for aggressive material removal and a smooth cut on the other for more precise finishing. Rough fitting and fine finishing capabilities are combined in a single file to help get jobs done faster.

2^{IN}1™



Special Tooth Construction
Tapers slightly toward the point to
reduce clogging

Consistently Precise Cut
Provides maximum material removal
per stroke and longer product life

Single Cut on Edges
Provides additional versatility

Double Cut on Sides
For faster material removal

21981N

Item No	Description	Package Type	Product Package Dimensions	Product Weight
21908N	8" 2 in 1 Flat Bastard and Smooth File	Carded	9.8" x 0.76" x 0.13"	0.21 lbs.
21910N	10" 2 in 1 Flat Bastard and Smooth File	Carded	12.25" x 0.96" x 0.15"	0.43 lbs.
21981N	8" and 10" 2 in 1 Flat Bastard and Smooth Files	Carded	12.25" x 0.96" x 0..28"	0.64 lbs.



WCSET3CMNNN

- Half round wood rasp for enlarging round surfaces
- Flat wood rasp for rapid stock removal
- Edge teeth for removal of materials in confined areas
- High quality steel chisel for cutting and scraping

Crescent Nicholson Files

Item No	Description	File Cut	Shape
WCSET3CMNNN	3 Pc. Chisel Rasp Set with CoMold Handle	4-IN-1 Tool	1/2 Round
05190N	14" Half Round Pipeliner File	Single Cut	1/2 Round
08642N	10"/254mm, Mill Bastard File	Single Cut	Rectangle
21857LN	8"/203mm, Half Round Bastard File without Handle, CDD	Double Cut	Flat / 1/2 Round
04995N	10"/254mm, Half Round Bastard File	Double Cut	Flat / 1/2 Round
21858N	10"/254mm, Half Round Bastard File without Handle, CDD	Double Cut	Flat / 1/2 Round
05094N	12"/305mm, Half Round Bastard File	Double Cut	Flat / 1/2 Round
05194N	14"/356mm, Half Round Bastard File	Double Cut	Flat / 1/2 Round
21474U	Universal Handle		



The Crescent APEX u-GUARD™ Non-Marring Covered Tools

The Crescent APEX series of u-GUARD™ non-marring covered tools gives you protection and control on the jobsite. These patented tools allow the user to grab directly onto the drive tool while it spins freely inside the cover, increasing fastening control and significantly reducing contact from the rotating tool.



NON-MARRING
Non-Marring Cover protects from scratching or damages; Thin Wall Maximizes access



SAFETY
Free Spinning Sleeve for enhanced control and safety



Superior Durability to withstand the toughest jobs

alphaCASE™ REFILL



Pivoting Insert Rails refillable for ease of use



Stackable for convenient storage



Full Length Metal Hinge for improved case life



Attachment Points for versatility on the job

Exterior Labels for visibility and marking

AUGSET-30 | Screwdriving bit tips include Square, Phillips®, Torx®, Slotted, Covered Quick Release Bit Holder, Covered Impact Power Bits, and Covered Magnetic Nutsetters

Part Number	Description	Drive End	Drive Size	Length
AUGBQ2A-1	u-Guard™ Covered Bit Holder	Bit Holder	1/4"	2-1/4"
AUGBH3-1	u-Guard™ Covered Bit Holder	Bit Holder	1/4"	3"
AUGB3BPH2-1	u-Guard™ Covered Impact Power Bit	Phillips	PH2	3"
AUMB3BPH2-1	u-Guard™ Covered Impact Power Bit	Phillips	PH2	3"
AUGB3BSQ2-1	u-Guard™ Covered Impact Power Bit	Square	SQ2	3"
AUMB3BSQ2-1	u-Guard™ Covered Impact Power Bit	Square	SQ2	3"
AUGB3BTX25-1	u-Guard™ Covered Impact Power Bit	Torx	T25	3"
AUMB3BTX25-1	u-Guard™ Covered Impact Power Bit	Torx	T25	3"
AUGN2B16-1	u-Guard™ Covered Magnetic Nutsetter	Hex Nutsetter	1/4"	2-9/16"
AUGN2B20-1	u-Guard™ Covered Magnetic Nutsetter	Hex Nutsetter	5/16"	2-9/16"
AUGN2B24-1	u-Guard™ Covered Magnetic Nutsetter	Hex Nutsetter	3/8"	2-9/16"
AUGN2B28-1	u-Guard™ Covered Magnetic Nutsetter	Hex Nutsetter	7/16"	2-9/16"
AUGN2B32-1	u-Guard™ Covered Magnetic Nutsetter	Hex Nutsetter	1/2"	2-9/16"
AUGN2BSET-1	u-Guard™ Covered Magnetic Nutsetter 3-Pc. Set	Hex Nutsetter	1/4", 5/16", 3/8"	2-9/16"
AUGSET-30	30 Piece u-Guard™ Fastening Set	—	—	—
AUGSET-38	30 Piece u-Guard™ Fastening Set	—	—	—

Phillips® is a registered trademark of the Phillips Screw Company. Torx® is a registered trademark of Acument Intellectual Properties, LLC.



Crescent
Mobile Showroom
 Contact your Crescent
 representative or local
 tool retailer to find out
 how you can bring it
 to your location!